
Rev	AWO #	Description	Date	Appr
-		RELEASED	1/13/05	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:
Material:
Insulator: Impact resistant Polypropylene, rated UL94–HB
Insulator color: Black
Spring: Steel, Nickel plated
Contacts: Steel, Nickel plated
Wire: 26 AWG, PVC
Electrical:
Operating voltage: 1.5 VDC max.
Temperature Rating:
Operating temperature: –10°C to +80°C
Environmental:
Lead free, RoHS comliant

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	SS	1/13/05
CHECKED		
APPROVED		

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: BATTERY HOLDER, WIRE LEADS FOR ONE "AA" CELL

SIZE	PART NO.	REV.
X	BH-01-4	-

REF: | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.