

Representative Image

Catalog No. 54140

Description: No4 CU LUG STD BRL 1HL 3/8IN GRY

UPC No 786210541402

Home > Connectivity & Grounding > Color Keyed / Blackburn > Cable or wire lug

Copper One-Hole Lug, Standard Barrel, Peep Hole, Max 35kV, Wire Size #4 AWG, 3/8 Inch Bolt Size, Tin Plated, Die Code 29, Die Color Code Gray

Descriptors

Category	Cable or wire lug

Specifications

Cable Size	4 AWG
Number Of Holes	1
Voltage Rating	35 kV
Insulation	None
Material	Copper
Color	Gray

Classifications

Brand Name	Color Keyed / Blackburn
Standard	UL E9809

Dimensions

Stud Size	3/8 in

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	180° (horizontal)
Slender flange model	N
Insulated	N
With sight-hole	Y

by ABB

Downloaded from Arrow.com.

ETIM	EC001051 Tube cable lug for copper conductors
Material	Copper
Surface protection	Tinned
Number of mounting holes	1
AWG size	4

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4503	622302	N/A	1097195_2015-02-20	N/A
CSA	7222	622302	N/A	N/A	N/A
UL	E9809	N/A	ZMVV	N/A	N/A

Downloaded from Arrow.com.