
**Part Number :** 2004530006
**Product Description :** Mini-Fit TPA2 Receptacle Housing, 4.20mm Pitch, Single Row, UL 94V-0, Low-Halogen, 6 Circuits
**Series Number :** 200453
**Status :** Active
**Product Category :** Connector Housings



## Documents and Resources

### Drawings

2004530006_sd.pdf

2004530000-PK-000.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

AS-172718-0000-001.pdf

PS-172718-0000-001.pdf

1727180001-TS-000.pdf

1727180002-TS-000.pdf

1727180003-TS-000.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Relevant |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Relevant |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Connector Housings |
| Series | 200453 |
| Description | Mini-Fit TPA2 Receptacle Housing, 4.20mm Pitch, Single Row, UL 94V-0, Low-Halogen, 6 Circuits |
| Application | Wire-to-Board, Wire-to-Wire |
| Comments | See product specification for current derating information. |
| Component Type | Receptacle |
| Product Name | Mini-Fit TPA2 |
| UPC | 889056445702 |

### Agency

| | |
|---|---|
| UL | E29179 |

### Physical

| | |
|---|---|
| Circuits (maximum) | 6 |
| Color - Resin | Black |
| Flammability | 94V-0 |
| Gender | Receptacle |

Downloaded from Arrow.com.

| | |
|---|---|
| Glow-Wire Capable | No |
| Keying to Mating Part | No |
| Lock to Mating Part | Yes |
| Material - Resin | Nylon |
| Net Weight | 1.550/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 4.20mm |
| Pitch - Termination Interface | 4.20mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| Mini-Fit TPA2 and Mini-Fit Sigma Single Row Plug Housings | 200471 |
| Mini-Fit TPA2 and Mini-Fit Sigma Single Row Plug Housings | 200488 |
| Mini-Fit Jr. Plug Housings | 5559 |
| Mini-Fit Jr. Vertical Headers | 5566 |
| Mini-Fit Jr. Right-Angle Headers | 5569 |

### Use with Part(s)

| Description | Part Number |
|---|---|
| Mini-Fit TPA2 Terminal Position Assurance (TPA) Retainer, 4.20mm Pitch, UL 94V-0, Low-Halogen, 6 Circuits, White | 1727090006 |
| Mini-Fit TPA2/Sigma Female Crimp Terminals | 172718 |
| Pre-Crimped Lead Mini-Fit Sigma/ TPA2 Female-to-Mini-Fit Sigma/ TPA2 Female | 219670 |

Downloaded from Arrow.com.

| | |
|---|---|
| Pre-Crimped Lead Mini-Fit Sigma/ TPA2 Female-to-Pigtail | 219671 |
| Mini-Fit TPA2/Sigma Female Crimp Terminals | 202988 |
| Mini-Fit TPA2 Connector Position Assurance (CPA) Retainers | 203603 |
| Mini-Fit TPA2/Sigma Female Low Mating Force Crimp Terminals | 221442 |



Downloaded from Arrow.com.