
SK 3,8 REEL P7,5 WH CUS - Marker card

0825127

https://www.phoenixcontact.com/us/products/0825127

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker card, can be ordered: by card, white, labeled according to customer specifications, mounting type: adhesive, for terminal block width: 7.5 mm

Your advantages

- Labeling service: Phoenix Contact can custom-label all SK ... markers in accordance with your requirements
- The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove

Commercial data

Item number	0825127
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	BG24
Product key	BG8113
GTIN	4046356354028
Weight per piece (including packing)	0.775 g
Weight per piece (excluding packing)	0.53 g
Customs tariff number	49119900
Country of origin	DE

Downloaded from Arrow.com.

Technical data

Notes

Order information:	Marking up to max. 25-pos.

Product properties

Product type	Klemmenmarker
Pitch	7.5 mm

Marking

Number of marker strips	12
Slot type	Label

Dimensions

Width	50.00 mm
Height	3.80 mm
Depth	0.07 mm
Pitch	7.5 mm

Material specifications

Foil strength	53 µm
Adhesive strength	20 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Ambient temperature (assembly)	> 15 °C
Recommended storage conditions	23 °C / 50% relative humidity. Storage in the original packaging is recommended prior to processing.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

Downloaded from Arrow.com.

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)


Mounting

Mounting type	adhesive

Downloaded from Arrow.com.

Drawings

Schematic diagram



① Horizontal
② Vertical

Downloaded from Arrow.com.

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761

UNSPSC

UNSPSC 21.0	39131500

Downloaded from Arrow.com.

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com

Downloaded from Arrow.com.