


Rev	AWO #	Description	Date	Appr
-		RELEASED	7/29/21	


APPROVED: _____


DATE: _____ TITLE: _____











SPECIFICATIONS:
Material:
Insulator: Nylon 66, rated UL 94V-0
Insulator color: Natural
Contacts: Brass
Plating:
Tin over Copper underplate overall
Electrical:
Current rating: 7A AC/DC
Contact resistance: 20 mohms max
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 1,500 VAC for 1 minute
Temperature Rating:
-25°C to +105°C
Environmental:
Lead free, RoHS compliant RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

DRAWN	JJ	7/29/21
CHECKED	YC	7/29/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE: .156 [3.96] POWER HEADER, RIGHT ANGLE WITH REAR LOCK, 5P, REMOVED PIN #02, #04

SIZE	PART NO.	REV.
X	LHC-A1-05-TRA-X02-X04-V0	-

REF:	SCALE:	SHEET
S00124T	NTS	1 OF 1

Downloaded from Arrow.com.