



**Part Number :** [747521258](#)

**Product Description :** SFP+-to-SFP+ Lite Passive Cable Assembly, 10Gbps, 30 AWG Cable, with Latch, 2.5m Length

**Series Number :** 74752

**Status :** Obsolete

**Product Category :** High-Speed I/O Cable Assemblies



---

## Documents and Resources


### Drawings

[747521258 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Obsolete
Category	High-Speed I/O Cable Assemblies
Series	74752
Description	SFP+-to-SFP+ Lite Passive Cable Assembly, 10Gbps, 30 AWG Cable, with Latch, 2.5m Length
Assembly Configuration	Dual Ended Connectors
Comments	Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths.
Connector to Connector	SFP+-to-SFP+
Product Name	SFP Plus,SFP+
UPC	889056738811

#### Agency

CSA	LR64395
UL	E72548

#### Electrical

Impedance	100Ω
-----------	------

#### Physical

Cable Length	2.50m
Circuits (Loaded)	TWO DIFFERENTIAL PAIR
Gender	Male-Male
Lock to Mating Part	Yes
Net Weight	101.424/g

Packaging Type	Bag
Single Ended	No
Wire/Cable Type	Twinax
Wire Size (AWG)	30

---

This document was generated on May 27, 2026

Obsolete