
Part Number : 640014100
Product Description : PremiumGrade Hand Crimp Tool for Flag Insulkrimp Quick Disconnect Terminals, 22-14 AWG
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools
Engineering Part Number : RHT-FIFG



Documents and Resources

Tooling Specifications

ATS-640014100-001.pdf
TM-640160065-001.pdf
TM-640160065CN-001.pdf
TM-640160065DE-001.pdf
TM-640160065SP-001.pdf
TM-640160065FR-001.pdf
TM-640160065IT-001.pdf
TM-640160065JP-001.pdf
TM-640160065KR-001.pdf
TM-640160065MY-001.pdf
TM-640160065PL-001.pdf
TM-640160065RU-001.pdf
TM-640160065SK-001.pdf
TM-640160065TH-001.pdf
TM-640160065VN-001.pdf
TM-640160065TW-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant

Downloaded from Arrow.com.

China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	PremiumGrade Hand Crimp Tool for Flag Insulkrimp Quick Disconnect Terminals, 22-14 AWG
Comments	Type RHT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	N/A
Tool Type	Hand Crimp Tool

Downloaded from Arrow.com.

UPC	822348071067
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Applicable Parts

Description	Part Number
Flag InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm^2) Wire, Box, Tab 6.35 x 0.81mm, Carton	190070001
Flag InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm^2) Wire, Box, Tab 4.75 x 0.51mm, Carton	190070009
Flag InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm^2) Wire, Box, Tab 4.75 x 0.81mm, Carton	190070015
Flag InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm^2) Wire, Box, Tab 6.35 x 0.81mm, Carton	190070021
Flag InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm^2)	190070029

Downloaded from Arrow.com.

Wire, Box, Tab 4.75 x 0.51mm, Carton	
Flag InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm^2) Wire, Box, Tab 4.75 x 0.81mm, Carton	190070035
InsulKrimp Female Fully Insulated Quick Disconnect Flag for 22-18 AWG Wire, Tab 6.35 x 0.81mm, 94 V-0 Material, Carton	190070064
InsulKrimp Female Fully Insulated Quick Disconnect Flag for 22-18 AWG Wire, Tab 4.75 x 0.51mm, 94 V-0 Material, Carton	190070067
InsulKrimp Female Fully Insulated Quick Disconnect Flag for 22-18 AWG Wire, Tab 4.75 x 0.81mm, 94 V-0 Material, Carton	190070070
InsulKrimp Female Fully Insulated Quick Disconnect Flag for 16-14 AWG Wire, Tab 6.35 x 0.81mm, 94 V-0 Material, Carton	190070073
InsulKrimp Female Fully Insulated Quick Disconnect Flag for 16-14 AWG Wire, Tab 4.75 x 0.51mm, 94 V-0 Material, Carton	190070076
InsulKrimp Female Fully Insulated Quick Disconnect Flag for 16-14 AWG Wire, Tab 4.75 x 0.81mm, 94 V-0 Material, Carton	190070079

Downloaded from Arrow.com.