
Part Number : 11030016
Product Description : Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals
Series Number : 207121
Status : Active
Product Category : Crimp Presses and Crimp Hand Tools
Engineering Part Number : HTA2174



Documents and Resources

Tooling Specifications

ATS-011030016-001.pdf
TM-638000029-001.pdf
TM-638000029DE-001.pdf
TM-638000029SP-001.pdf
TM-638000029FR-001.pdf
TM-638000029IT-001.pdf
TM-638000029JP-001.pdf
TM-638000029KR-001.pdf
TM-638000029MY-001.pdf
TM-638000029PL-001.pdf
TM-638000029RU-001.pdf
TM-638000029SK-001.pdf
TM-638000029TH-001.pdf
TM-638000029VN-001.pdf
TM-638000029CN-001.pdf
TM-638000029TW-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant

Downloaded from Arrow.com.

Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207121
Description	Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals
Comments	See Tooling Specification (PDF) Above
Function	Extraction
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	Flat Blade,KK,KK 396,MarKK,Mini-Lock,Trifurcon,Ultra-Fit
Tool Type	Extraction Hand Tool

Downloaded from Arrow.com.

UPC	800753619951
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Applicable Parts

Description	Part Number
Flat Blade Crimp Terminal, Series 1508, Female, With Tin (Sn) Plated Brass Contact, Single 20-14 AWG or Double 18+18 or 20+20 AWG, Reel	05060117
KK 396 Female Crimp Terminal, 24-18 AWG, Reel, Brass, 2.54µm Hot Tin (Sn) Dip Plated	08500105
KK 396 Female Crimp Terminal, 24-18 AWG, Bag, Brass, 2.54µm Hot Tin (Sn) Dip Plated	08500106
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Brass, 2.540µm Tin (Sn)	08500107
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Brass, 2.540µm Tin (Sn)	08500108
KK 396 Crimp Terminal 2578,	08500111

Downloaded from Arrow.com.

26-22 AWG, Reel, Brass, 2.54µm Tin (Sn)	
KK 396 Female Crimp Terminal, 24-18 AWG, Reel, Brass, 3.81µm Tin (Sn) Plated	08500119
KK 396 Female Crimp Terminal, 24-18 AWG, Bag, Brass, 3.81µm Tin (Sn) Plated	08500120
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Phosphor Bronze, 2.540µm Tin (Sn)	08500133
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Phosphor Bronze, 2.540µm Tin(Sn)	08500134
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Reel, Brass Tin (Sn)	08500183
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Bag, Brass Tin (Sn)	08500185
KK Trifurcon Crimp Terminal 6838, 20-18 AWG, Reel, Brass Tin (Sn)	08500187
KK Trifurcon Crimp Terminal 6838, 20-18 AWG, Bag, Brass Tin (Sn)	08500189
KK 396 Female Crimp Terminal, 24-18 AWG, Reel, Phosphor Bronze, 3.81µm Tin (Sn) Plated	08500281
KK 396 Female Crimp Terminal, 24-18 AWG, Reel, Phosphor Bronze, 2.54µm Hot Tin (Sn) Dip Plated	08520071
KK 396 Female Crimp Terminal , 24-18 AWG, Bag, Phosphor Bronze, 2.54µm Hot Tin (Sn) Dip Plated	08520072
KK Trifurcon Crimp Terminal 6838, 20-18 AWG, Reel, Phosphor Bronze Tin(Sn)	08520112
KK Trifurcon Crimp Terminal 6838, 20-18 AWG, Bag, Phosphor	08520113

Downloaded from Arrow.com.

Bronze Tin (Sn)	
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Reel, Phosphor Bronze Tin(Sn)	08520124
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Bag, Phosphor Bronze Tin (Sn)	08520125
KK 396 Female Crimp Terminal, 24-18 AWG, Reel, Phosphor Bronze, 2.54µm Tin (Sn) Plated	08520811
KK 396 Female Crimp Terminal, 24-18 AWG, Bag, Phosphor Bronze, 2.54µm Tin (Sn) Plated	08520812
KK 396 Female Crimp Terminal, 24-18 AWG, Reel, Brass, 0.38µm Selective Gold (Au) Plated	08550103
KK 396 Female Crimp Terminal, 24-18 AWG, Bag, Brass, 0.38µm Selective Gold (Au) Plated	08550104
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Brass, 0.38µm Selective Gold (Au)	08550105
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Brass, 0.38µm Selective Gold(Au)	08550106
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Brass, 0.76µm Select Gold (Au) over Gold Flash	08550123
KK 396 Female Crimp Terminal, 24-18 AWG, Reel, Brass, 0.76µm Selective Gold (Au) Plated	08550133
KK 396 Female Crimp Terminal, 24-18 AWG, Bag, Brass, 0.76µm Selective Gold (Au) Plated	08550134
KK 396 Crimp Terminal 2578, 26-22 AWG, Left Payoff Reel, Brass, 0.76µm Select Gold (Au) over Gold Flash	08550137
KK 396 Female Crimp Terminal, 24-18 AWG, Reel, Brass, 0.51µm Selective Gold (Au) Plated	08560105

Downloaded from Arrow.com.

KK 396 Female Crimp Terminal, 24-18 AWG, Bag, Brass, 0.51µm Selective Gold (Au) Plated	08560106
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Brass, 0.38µm Select Gold (Au) over Gold Flash	08560107
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Brass, 0.38µm Select Gold (Au) over Gold Flash	08560108
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Reel, Phosphor Bronze Gold (Au)	08560123
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Bag, Phosphor Bronze Gold(Au)	08560124
KK Trifurcon Crimp Terminal 6438, 20-18 AWG, Reel, Phosphor Bronze Selective Gold (Au)	08580110
KK Trifurcon Crimp Terminal 6438, 20-18 AWG, Bag, Phosphor Bronze Selective Gold (Au)	08580111
KK 396 Female Crimp Terminal, 24-18 AWG, Reel, Phosphor Bronze, 0.76µm Selective Gold (Au) Plated	08580114
KK 396 Female Crimp Terminal, 24-18 AWG, Bag, Phosphor Bronze, 0.76µm Selective Gold (Au) Plated	08580115
KK 396 Female Crimp Terminal, 24-18 AWG, Reel, Phosphor Bronze, 0.51µm Selective Gold (Au) Plated	08580121
KK 396 Female Crimp Terminal, 24-18 AWG, Bag, Phosphor Bronze, 0.51µm Selective Gold (Au) Plated	08580122
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Phosphor Bronze, 0.38µm Selective Gold (Au) over Gold Flash	08580125
KK 396 Crimp Terminal 2578,	08580126

Downloaded from Arrow.com.

26-22 AWG, Bag, Phosphor Bronze, 0.38µm Selective Gold (Au) over Gold Flash	
KK Trifurcon Crimp Terminal 6438, 20-18 AWG, Reel, Phosphor Bronze Gold (Au)	08580187
KK Trifurcon Crimp Terminal 6438, 20-18 AWG, Bag, Phosphor Bronze Gold(Au)	08580189
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Phosphor Bronze, 3.810µm Tin (Sn)	08600003
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Phosphor Bronze, 3.810µm Tin (Sn)	08600004
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Phosphor Bronze, 0.76µm Select Gold (Au) over Gold Flash	08650110
KK 396 Female Crimp Terminal, 24-18 AWG, Reel, Phosphor Bronze, 0.38µm Selective Gold (Au) Plated	08650114
KK 396 Female Crimp Terminal, 24-18 AWG, Bag, Phosphor Bronze, 0.38µm Selective Gold (Au) Plated	08650115
KK 396 Crimp Terminal 2578, 26-22 AWG, Reel, Phosphor Bronze, 0.38µm Selective Gold (Au)	08650116
KK 396 Crimp Terminal 2578, 26-22 AWG, Bag, Phosphor Bronze, 0.38µm Selective Gold (Au)	08650117
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Reel, Phosphor Bronze Selective Gold (Au)	08650121
KK Trifurcon Crimp Terminal 7258, 26-22 AWG, Bag, Phosphor Bronze Selective Gold (Au)	08650122
KK 396 Female Crimp Terminal,	39000286

Downloaded from Arrow.com.

24-18 AWG, Reel, Brass, 0.90µm Pre-Plated Tin (Sn) Plated	
Female Crimp Terminal for 3.96mm Pitch Housing, 20-18 AWG, Pre-Tinned Plating, Reel	455703000
Female Crimp Terminal for 3.96mm Pitch Housing, 20-18 AWG, Tin (Sn) over Nickel (Ni) Plating, Reel	455703002
3.96mm (.156”) Pitch MarKK Crimp Terminal, 20-18 AWG, Tin (Sn) over Nickel (Ni) With Select Gold (Au) Plating, Reel	455703004
Female Crimp Terminal for 3.96mm Pitch Housing, 20-18 AWG, Pre-Tinned Plating, Bag	455703050
Female Crimp Terminal for 3.96mm Pitch Housing, 20-18 AWG, Tin (Sn) over Nickel (Ni) Plating, Bag	455703052
3.96mm (.156”) Pitch MarKK Crimp Terminal, 20-18 AWG, Tin (Sn) over Nickel (Ni) With Select Gold (Au) Plating, Bag	455703054
Icemaker Crimp Terminal Humpback with Anti-Fish Hook	456060004
2.00mm Pitch Crimp Terminal, Male, Phosphor Bronze, 0.76µm Gold (Au) Plating, Reel	506398028
2.00mm Pitch Crimp Terminal, Male, Phosphor Bronze, 0.76µm Gold (Au) Plating, Bag	506398128
2.50mm Pitch, Mini-Lock Male Crimp Terminal, Tin Plating, 28-22 AWG, Reel	508378000
2.50mm Pitch, Mini-Lock Male Crimp Terminal, Tin Plating, 28-22 AWG, Bag	508378100
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, Tin (Sn) Plating, Double 16+16 or Single 12 AWG, Reel	768230343

Downloaded from Arrow.com.

Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, Tin (Sn) Plating, Double 20+20, 18+18 or Single 16-14 AWG, Reel	768230344
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, Tin (Sn) Plating, 10 AWG, Reel	768230345
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.38µm Gold (Au) Plating, Double 16+16 or Single 12 AWG, Reel	1720630333
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.38µm Gold (Au) Plating, Double 20+20, 18+18 or Single 16-14 AWG, Reel	1720630334
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.38µm Gold (Au) Plating, 10 AWG, Reel	1720630335
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.76µm Gold (Au) Plating, Double 16+16 or Single 12 AWG, Reel	1720631333
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.76µm Gold (Au) Plating, Double 20+20, 18+18 or Single 16-14 AWG, Reel	1720631334
Mega-Fit Tangless TPA-Capable Crimp Terminal, Female, 0.76µm Gold (Au) Plating, 10 AWG, Reel	1720631335
3.96mm Pitch EdgeMate Crimp Terminal, Phosphor Bronze, Tin (Sn), Bifurcated, 20-18 AWG, Reel	1721601803
3.96mm Pitch EdgeMate Crimp Terminal, Brass, Gold (Au), Bifurcated, 20-18 AWG, Reel	1721601805

Downloaded from Arrow.com.