


DB25 Female

Configuration:

DB25M	DB25F
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
10	10
11	11
12	12
13	13
14	14
15	15
16	16
17	17
18	18
19	19
20	20
21	21
22	22
23	23
24	24
25	25
Shield	Shield

Material:

- Cable: #28, 25C+1+AL/MY O.D.:6.5
- Connector: DB25M, Blue
DB25F, Blue
- Thumbscrew: #4-40UNC

Note:

- Total Length: See "Item No."
- Color: Beige
- Molded Type

Scale	1:1						Name	Item No.		
TOLERANCE					Drawn	11.14.11	Chappell	AK135-2 (2M) AK136-5 (5M)		
X.X	±0.40							AK166-3 (3M) AK168-10 (10M)		
X.XX	±0.25				Approved			Title Serial / Parallel Extension Cable, D-Sub 25 Pin Male to D-Sub 25 Pin Female		
X.XXX	±0.15									
Angle	±3°							Drawing No.		
										rev00
			Modification	Date	Name			Replace		
								Sheet		

RoHS
Compliant

ASSMANN
components