


REV.	DATE	DESCRIPTION
NC	04/06/06	INITIAL RELEASE



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex					
7						DRAWN	G.R.S.	04/06/06							
6						CHECKED				PART DESCRIPTION SMA END LAUNCH SURFACE MOUNT RECEPTACLE					
5						ISSUED									
4						SHEET		1 OF 1							PART NO. 132372
3	CONTACT PIN	BER. COPPER	GOLD	1											
2	INSULATOR	TEFLON	NATURAL	1							DWG. NO. 132372.DWG				
1	BODY	BRASS	GOLD	1											
DESCRIPTION MATERIAL FINISH QTY					CAD FILE C:/132/1132372.DWG										