

38CHENBOX, 3/8" Hex Nut, Silicon Bronze

By Burndy
Catalog # 38CHENBOX



Silicon Bronze NUT ,3/8 Stud ,Thread series-Class 28.

Features

- DURIUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

Application

Used to fasten the joints

General

Catalog Number	38CHENBOX
Connector Type	Nut
EU RoHS Indicator	Yes
Installation Torque	180 LBS/in
Recommended in-lb	
Material	SILICON BRONZE
Sub Brand	DURIUM
Trade Name	DURIUM™
Type	HARDWARE
UPC	781810012383
UPC 14 Digit GTIN	00781810012383

Dimensions

Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.375 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Thread Size	3/8-16
Dimension - Threads per inch	16

Certifications And Compliance

Buy America(n) Qualified	Buy American Act Compliant (All status valid till December 2024)
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	48000

Product Assets

[3D Models - 38CHENBOX_MODEL-STEP](#)
[3D Models - 38CHENBOX_MODEL-PDF](#)
[3D Models - 38CHENBOX_MODEL-IGES](#)
[Catalogs - BURNDY Master Catalog - Section F - Accessories](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_38CHENBOX_LineArt](#)
[Sales Drawings - wsc206494-01](#)
[Specifications - 38CHENBOX](#)