Part Number : 1301460130
Product Description : Watertite Extreme Extra Hard Outdoor Receptacle with Single Flip Coverplate, 2 Pole/3 Wire, NEMA 5-15, 125V, Black
Series Number : 130146
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 60W47BLK



Documents and Resources

Drawings

1301460130_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Extra Hard Outdoor Receptacle with Single Flip Coverplate, 2 Pole/3 Wire, NEMA 5-15, 125V, Black
IP Rating	IP67
NEMA Configuration	NEMA 5-15
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678831084

Agency

UL	E68122

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	125V

Physical

Cord Type	N/A
Flange	No

Downloaded from Arrow.com.

Flip Lid	Yes
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	No
Poles	2-pole/3-wire
Receptacle Type	Single

Downloaded from Arrow.com.