
7906 Series

D-SUB Right Angle Type



Material:

Housing: Thermoplastic Polyester Glass Filled UL94V-0.
Contacts: Copper Alloy.
Shell: Metal.


Electrical Characteristics:

Current Rating: 1 A.
Dielectric Withstanding Voltage: AC 1000V.
Insulator Resistance: 1000MΩ min.
Contact Resistance: 30mΩ max.
Operating Temperature: -55°C~+105°C.


Features:


Mates with: 7901,7907, 7908.


Male





Female














P.C. Board Layout

Position	Dimension			
	A	B	C	D
9	16.92	24.99	30.81	16.33
15	25.25	33.32	39.14	24.66
25	38.96	47.04	53.04	38.38
37	55.42	63.50	69.32	54.84

Ordering information

7906-	37	M	A	A
Series	Position	M: Male F: Female	A ~ Z: See Page A152 ~ A153	A: Tray Package

Downloaded from Arrow.com.