

har-port USB 2.0 A-A ; PFT white



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 452 1918
Specification	har-port USB 2.0 A-A ; PFT white
HARTING eCatalogue	https://harting.com/09454521918

Identification

Category	Connectors
Series	har-port
Element	Service interfaces
Specification	USB 2.0

Version

Connection type	Type A jack - type A jack
Fixing	Screwable in cover plates

Technical characteristics

Ambient temperature	-25 ... +70 °C
Mating cycles	≥1,500
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	White
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	13 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140222878
eCl@ss	27060304 Appliance cord (data cable)
ETIM	EC002599
UNSPSC 24.0	43202222