
Part Number : 352841010
Product Description : 2.28mm Tab Wire-to-Wire Uniconn Housing, Female, 10 Circuits
Series Number : 35284
Status : Obsolete
Product Category : Connector Housings



Documents and Resources

Drawings

352841010_sd.pdf

Specifications

PK-35284-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Obsolete

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Connector Housings
Series	35284
Description	2.28mm Tab Wire-to-Wire Uniconn Housing, Female, 10 Circuits
Application	Wire-to-Wire
Component Type	Receptacle
Product Name	Uniconn
UPC	800754843171

Physical

Circuits (maximum)	10
Color - Resin	Black, Natural
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Polyester
Net Weight	5.330/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.81mm
Temperature Range - Operating	-40° to +80°C

Obsolete

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.28mm Tab Wire-to-Wire Uniconn Housings	35282

Use with Part(s)

Downloaded from Arrow.com.

Description	Part Number
Tab Terminals	35420
Tab Terminals	35421

This document was generated on Sep 09, 2026

Obsolete

Downloaded from Arrow.com.