Part Number : 1060598108
Product Description : Optical Industrial Plug Connector, Plastic Body, LC, Single Mode
Series Number : 86389
Status : Obsolete
Product Category : Fiber Optic Connectors



Obsolete

Documents and Resources

Drawings

1060598108_sd.pdf

Specifications

1060598000-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Fiber Optic Connectors
Series	86389
Description	Optical Industrial Plug Connector, Plastic Body, LC, Single Mode
Mode	Singlemode
Product Name	Industrial LC
UPC	887191335773

Physical

Angled Physical Contact (APC)	No
Boot Color	N/A
Boot Type	N/A
Cable Size	8.00mm max.
Color - Resin	Black
Ferrule Hole Size	125.5µm
Ferrule Material	Ceramic
Gender	Plug
Material - Housing	Polymer
Mounting Style	Bayonet
Net Weight	52.950/g
Ports	2
Wire/Cable Type	Fiber Optic - 2 Fiber

Mates With / Use With

Mates with Part(s)

Description	Part Number

Obsolete

Downloaded from Arrow.com.

Fiber Optic Connectors, Adapters, and Accessories	106059
Industrial Simplified SFP Receptacles	106501

This document was generated on May 27, 2026

Obsolete

Downloaded from Arrow.com.