

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION – –, .
© COPYRIGHT 2010 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST
DW	


REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED AS PER ECN-22-176158	22JUL'22	HS	SZ















NOTE:

1. MATERIAL:
   HOUSING: PA9T, UL 94V-0, BLACK COLOR.
   CAP: LCP, UL 94V-0, BLACK COLOR.
   CONTACTS: PHOSPHOR BRONZE.
   SHELL: PHOSPHOR BRONZE.
2. FINISH:
   CONTACTS: 0.762μm [30μ"] MIN. GOLD PLATED ON CONTACT AREA,
   2.54μm [100μ"] MIN. MATTE TIN PLATED ON SOLDER TAIL,
   1.27μm [50μ"] MIN. NICKEL UNDERPLATED ALL OVER.
   SHELL: 2.54μm [100μ"] MIN. BRIGHT TIN PLATED OVER
   1.27μm [50μ"] MIN. NICKEL UNDERPLATED ALL OVER.
3. OPTION PART : CAP
4. REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC. 109-201, CONDITION B.
5. CAP WEIGHT : 0.789 gram



RECOMMENDED PCB LAYOUT (THICKNESS:1.6mm)
(DIMENSION TOLERANCE: 1PLC:±0.1 2PLC:±0.05)
KEEP OUT AREA FOR HOUSING STAND OFF

WITH	2041517-2
W/O	2041517-1
CAP 3	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± –
1 PLC	± 0.30
2 PLC	± 0.20
3 PLC	± 0.15
4 PLC	± –
ANGLES	± 3°

MATERIAL: SEE NOTE
FINISH: SEE NOTE

DWN	J. CHEN	01JUN2012
CHK	S. CHIEN	01JUN2012
APVD	W. KODAMA	01JUN2012
PRODUCT SPEC	108-57912	
APPLICATION SPEC	—	
WEIGHT	0.725 g	

TE Connectivity

NAME: MINI USB CONNECTOR, RECEPTACLE VERTICAL, DIP, B TYPE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2041517	—

CUSTOMER DRAWING | SCALE — | SHEET 1 OF 3 | REV B

1470-19 (1/08)


Downloaded from Arrow.com.

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT 2010 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST
DW	—


REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			




NOTE:
1. MATERIAL:
   COVER TAPE: PET, WHITE COLOR.
   CARRIER TAPE: PS.
   REEL: PS.
   SHIPPING BOX: CORRUGATED FIBER.
2. DIMENSION:
   REEL: SEE DRAWING.
   SHIPPING BOX: SEE DRAWING.
3. QUANTITY: SEE TABLE.
4. WEIGHT: SEE TABLE
5. PEELING RESISTANCE: 10gf ~ 130gf
6. PEELING SPEED: 300mm/MINUTE.







PACKAGING PROCESS



12.5 KG	9.13 KG	1200	10	12000	2041517–1
GROSS WEIGHT	NET WEIGHT	PCS /REEL	REELS /BOX	QUANTITY	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± –
1 PLC	± 0.30
2 PLC	± 0.30
3 PLC	± 0.30
4 PLC	± –
ANGLES	± –

MATERIAL –

FINISH –

DWN –
CHK –
APVD –
PRODUCT SPEC –
APPLICATION SPEC –
WEIGHT –

TE Connectivity

NAME
MINI USB CONNECTOR, RECEPTACLE
VERTICAL, DIP, B TYPE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2041517	—

CUSTOMER DRAWING | SCALE — | SHEET 2 OF 3 | REV B

1470–19 (1/08)


Downloaded from Arrow.com.

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT 2010 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST
DW	—


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			



NOTE:
1. MATERIAL:
   COVER TAPE: PET, WHITE COLOR.
   CARRIER TAPE: PS.
   REEL: PS.
   SHIPPING BOX: CORRUGATED FIBER.
2. DIMENSION:
   REEL: SEE DRAWING.
   SHIPPING BOX: SEE DRAWING.
3. QUANTITY: SEE TABLE.
4. WEIGHT: SEE TABLE
5. PEELING RESISTANCE: 10gf ~ 130gf
6. PEELING SPEED: 300mm/MINUTE.





PACKAGING PROCESS

6.70KG	2.60 KG	300	10	3000	2041517–2
GROSS WEIGHT	NET WEIGHT	PCS /REEL	REELS /BOX	QUANTITY	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± –
1 PLC	± 0.30
2 PLC	± 0.30
3 PLC	± 0.30
4 PLC	± –
ANGLES	± –

MATERIAL: –

FINISH: –

DWN	–
CHK	–
APVD	–
PRODUCT SPEC	—
APPLICATION SPEC	—
WEIGHT	—

TE Connectivity

NAME: MINI USB CONNECTOR, RECEPTACLE VERTICAL, DIP, B TYPE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2041517	—

CUSTOMER DRAWING | SCALE — | SHEET 3 OF 3 | REV B

Downloaded from Arrow.com.