
Part Number : 441330800
Product Description : Micro-Fit BMI Receptacle Housing, Dual Row, Panel Mount, 8 Circuits, Polyester, UL 94V-0
Series Number : 44133
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

441330800_sd.pdf

PK-44133-002-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

443000001-AS-000.pdf

444280001-AS-000.pdf

PS-44300-001-001.pdf

TS-43045-001-001.pdf

TS-43045-002-001.pdf

447640002-TS-000.pdf

TS-46235-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC

Downloaded from Arrow.com.

	61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	44133
Description	Micro-Fit BMI Receptacle Housing, Dual Row, Panel Mount, 8 Circuits, Polyester, UL 94V-0
Application	Wire-to-Board, Wire-to-Wire
Component Type	Housing
Product Name	Micro-Fit BMI
UPC	800754807975

Agency

CSA	LR19980
UL	E29179

Physical

Downloaded from Arrow.com.

Circuits (maximum)	8
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	No
Material - Resin	Polyester
Net Weight	2.225/g
Number of Rows	2
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-Fit BMI Plug Housing, Dual Row, Panel Mount, 8 Circuits, Black	443000800
Micro-Fit BMI Right-Angle Dual Row Headers	44428
Micro-Fit BMI Vertical Dual Row Headers	44432
Micro-Fit BMI CPI Vertical Dual Row Headers	45280

Use with Part(s)

Description	Part Number
Pre-Crimped Lead Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female, Tin (Sn) Plating, 150.00mm	797580002

Downloaded from Arrow.com.

Length, 20 AWG, Black	
Pre-Crimped Lead Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female, Gold (Au) Plating, 150.00mm Length, 20 AWG, Black	797580004
Pre-Crimped Lead Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female, Tin (Sn) Plating, 300.00mm Length, 20 AWG, Black	797580010
Pre-Crimped Lead Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female, Gold (Au) Plating, 300.00mm Length, 20 AWG, Black	797580012
Micro-Fit 3.0 Female Crimp Terminals	43030
Micro-Fit 3.0 Female Crimp Terminals with Lubricant	45773
Micro-Fit Reduced Mating Force Female Crimp Terminals	46235
Pre-Crimped Lead Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female	214760
Pre-Crimped Lead Micro-Fit 3.0 Female-to-Pigtail	214761

Downloaded from Arrow.com.