

## Printer - BLUEMARK CLED - 5147999

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Printers with LED-UV technology for printing plastic labels in UniCard format.

### Why buy this product

- ✓ Easy and time-saving operation
- ✓ The printer detects the direction of the inserted sheets and automatically rotates printing 180° if required
- ✓ Instant wipe resistance, making the labels ready for immediate use
- ✓ Fast labeling of plastic labels for terminal, conductor, cable, and device marking applications
- ✓ Solvent-free labeling of up to 10,000 markers per hour
- ✓ Environmentally-friendly high-speed printer with modern UV technology
- ✓ Automatic material feed
- ✓ Can be networked via Ethernet

RoHS

### Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 586177
GTIN	4046356586177
Custom tariff number	84433210
Country of origin	Germany

### Technical data

#### General

Interface	10/100 Mbps Ethernet
	USB 2.0
Weight	16.00 kg

# Printer - BLUEMARK CLED - 5147999

## Technical data

### Dimensions

Length	500.00 mm
Height	330.00 mm
Width	480.00 mm

### Connection data

Minimum voltage	100 V AC
Max. voltage	240 V AC
Additional text	50 Hz ... 60 Hz

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Classifications

### eCl@ss

eCl@ss 4.0	24190103
eCl@ss 4.1	24190103
eCl@ss 5.0	19029102
eCl@ss 5.1	19029102
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	19140190
eCl@ss 9.0	19140190

### ETIM

ETIM 4.0	EC001045
ETIM 5.0	EC001672
ETIM 6.0	EC001672

### UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43212110

Printer - BLUEMARK CLED - 5147999

Approvals

Approvals

Approvals

EAC / EAC / KC / EAC

Ex Approvals

Approval details

EAC		EAC-Zulassung
EAC		7500651.22.01.00240
KC		<a href="http://eng.kcc.go.kr/user/ehpMain.do">http://eng.kcc.go.kr/user/ehpMain.do</a> KCC-REI- PCK-FL514799
EAC		RU *- DE.A*30.B.02513

Accessories

Accessories

Magazine

Magazine - BLUEMARK CLED-MAG 20 - 5146655



Magazine for the BLUEMARK CLED printer, for accommodating 20 UC-... or 20 UCT-... sheets

## Printer - BLUEMARK CLED - 5147999

### Accessories

Magazine - BLUEMARK CLED-MAG 40 - 5146668



Magazine for the BLUEMARK CLED printer, for accommodating 40 UC-... or 40 UCT-... sheets

---

Magazine - BLUEMARK MAG AI-WM - 5146567



Magazine for BLUEMARK printer, for accommodating 0.5 - 1.5 mm² ferrules with insulating collar that can be labeled

---

Magazine - BLUEMARK MAG AI-WM 2,5 - 5146640



Magazine for BLUEMARK printer, for accommodating 2.5 mm² ferrules with insulating collar that can be labeled

---

Magazine - BLUEMARK MAG BN-ZB - 5146192

Magazine

---

Magazine - BLUEMARK MAG EM-M (100X60) - 0802742



Magazine, length: 120 mm, width: 76 mm, color: white

---

## Printer - BLUEMARK CLED - 5147999

### Accessories

Magazine - BLUEMARK MAG EM-M (27X18) - 0802737



Magazine, length: 120 mm, width: 76 mm, color: white

---

Magazine - BLUEMARK MAG EM-M (27X15) - 0802736



Magazine, length: 120 mm, width: 76 mm, color: white

---

Magazine - BLUEMARK MAG EM-M (49X15) - 0802738



Magazine, length: 120 mm, width: 76 mm, color: white

---

Magazine - BLUEMARK MAG EM-M (60X15) - 0802739



Magazine, length: 120 mm, width: 76 mm, color: white

---

Magazine - BLUEMARK MAG EM-M (60X30) - 0802740



Magazine, length: 120 mm, width: 76 mm, color: white

---

## Printer - BLUEMARK CLED - 5147999

### Accessories

Magazine - BLUEMARK MAG EM-M (85,6X54) - 0802741



Magazine, length: 120 mm, width: 76 mm, color: white

---

Magazine - BLUEMARK MAG WM-M (29X8) - 0802743



Magazine, length: 120 mm, width: 76 mm, color: white

---

Magazine - BLUEMARK MAG WM-M (40X15) - 0802744



Magazine, length: 120 mm, width: 76 mm, color: white

---

Magazine - BLUEMARK MAG WM-M (60X15) - 0802746



Magazine, length: 120 mm, width: 76 mm, color: white

---

Magazine - BLUEMARK MAG WM-M (D30) - 0802747



Magazine, length: 120 mm, width: 76 mm, color: white

---

Magazine - BLUEMARK MAG ZB - 5146529

Magazine for BLUEMARK, only for ZB 7,62 UV-100 - 0829029

## Printer - BLUEMARK CLED - 5147999

### Accessories

---

#### Magazine - BLUEMARK MAG ZB 8/27 - 5146558

Magazine for BLUEMARK, only for ZB 8/27 UV-100 - 0829102

---

### Planning and marking software

#### Software - CLIP-PROJECT ADVANCED - 5146040



Multilingual software for convenient configuration of Phoenix Contact products on standard DIN rails.

---

#### Software - CLIP-PROJECT PROFESSIONAL - 5146053



Multilingual software for terminal strip configuration. A marking module enables the professional marking of markers and labels for identifying terminal blocks, conductors and cables, and devices.

---

### Printing system accessories

#### Stackable housing - BLUEMARK CLED-STACKER 20 - 5146656



Stackable housing for the BLUEMARK CLED printer, for accommodating 20 UC-... or 20 UCT-... sheets

---

#### Accommodating box for marker sheets - BLUEMARK CLED-BASE - 5146669



Accommodating box, in conjunction with the BLUEMARK CLED-MAG 40, for accommodating 90 UC or UCT sheets

---

## Printer - BLUEMARK CLED - 5147999

### Accessories

Ink cartridge - BLUEMARK CLED-FLUID-CARTR. - 5146662



Cartridge, for replacement, 20 ml UV color, black, including cleaning cartridge

---

Case - BLUEMARK CLED CASE - 5146725



Case for the BLUEMARK CLED printer

---

Cable set - BLUEMARK CLED-CABLE-SET - 5146661

Cable set

---

Original packaging - BLUEMARK CLED-CARDBOARD-BOX - 5146660

Original packaging

---

Ink cartridge - BLUEMARK CLED-DUMMY-CARTR. - 5146659

Dummy ink cartridge for the BLUEMARK CLED printer

---