




PRODUCT NUMBER	PITCH
EPxx00000J0G	5.00 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material:

- Item @ Terminal body: Thermoplastic Black Color UL94V-0
- Item ⑤ Pin : Brass , Tin plated

Electrical:

- Voltage rating: 300V
- Current rating: 15A
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus

N=NUMBER OF POLES

Dim L=N×5.00	
Dim B=(N-1)×5.00	
POLES	Tolerance
2P-5P	±0.10
6P-10P	±0.15
11P-15P	±0.20
16P-20P	±0.25
21P-24P	±0.30

PART NO.: EP xx 0 0 0 0 0 0 J0 G

Solid block
No. of poles
02 2 poles
03 3 poles
...
24 24 poles

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface	tolerance	projection	product family
Itr	ecn	no	dr	ASME Y14.5	ASME Y14.5		TERMINAL BLOCK
				tolerances unless otherwise specified			
				angles	X.±0.5		
				edges	X.X±0.3	MM	
				XX.±1°	X.XX±0.1	scale	
			dr	EVIN ZHONG	041714		
			engr	EVIN ZHONG	041714		
			chr	HANKE FENG	041714		
			appd	SHI JUN	041714		
sheet	revision	A					
index	sheet	1					

