

COAXIAL CONNECTOR, UHF, X Ohm, Straight panel receptacle, jack (female), flange mount  
23\_UHF-0-0-2/033\_

**Properties**

- Mateable with 4 mm banana plugs
- Applicable in frequencies up to 200 MHz



| Product configuration       |            |                             |
|-----------------------------|------------|-----------------------------|
| Interface type              | Gender     | Standard                    |
| UHF                         | jack       | IEC 60169-12                |
|                             |            |                             |
| Interface and material data |            |                             |
| Piece parts                 | Material   | Plating                     |
| Centre contact              | Brass      | Silver Plating              |
| Outer conductor             | Brass      | SUCOPLATE (R) Plating       |
| Body                        | Brass      | SUCOPLATE (R) Plating       |
| Insulator                   | PFA / PTFE |                             |
|                             |            |                             |
| Electrical data             |            |                             |
| Interface frequency         |            | 0.2 GHz                     |
|                             |            |                             |
| Mechanical data             |            |                             |
| Weight                      |            | 0.0233 kg                   |
| Mating cycles               |            | 500                         |
| Flange type                 |            | square flange / 25.4 X 25.4 |
| Tab style                   |            | solder end                  |
|                             |            |                             |
| Environmental data          |            |                             |
| Operation temperature       |            | -55 °C ... 165 °C           |

**COAXIAL CONNECTOR, UHF, X Ohm, Straight panel receptacle, jack (female), flange mount**  
23\_UHF-0-0-2/033\_

| Material compliance        |                                   |                                 |                      |
|----------------------------|-----------------------------------|---------------------------------|----------------------|
| Item number                | Directive / Regulation            | Rating                          | Exemptions / Details |
| 22542788                   | RoHS 2011/65/EU and (EU) 2015/863 | Compliant with exemption        | 6c                   |
|                            | REACH 1907/2006 Article 33 SVHC   | Contains one or more SVHC >0,1% | CAS: 7439-92-1 Lead  |
| Ordering Information Table |                                   |                                 |                      |
| Item number                | Item description                  |                                 | Packaging type       |
| 22542788                   | 23_UHF-0-0-2/033_-E               |                                 | Single               |

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.  
DOCUMENT PIM-P2689 / Date of publication: 12.07.2025 / uncontrolled copy