

1

2

3

4

A

B

C





D

A


B

C

D



PC board drilling dimensions
(after plating - thickness: 1.60 to 3.20 mm)



TIN LEAD PART NUMBER

D50S90C4PA00	D50S90C6PA00
Gold flash	0,76 µ gold

LEAD FREE PART NUMBER

D50S90C4PA00LF	D50S90C6PA00LF
Gold flash	0,76 µ gold

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

European Views

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 		
TOLERANCES UNLESS OTHERWISE SPECIFIED											
Dr	M	PESSON	2006/01/11	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2		
Eng	P	LEGARE	2006/01/11			0.XX	±0.1				
Chr	-	-	0.XX' ±2'			0.XXX	±0.1				
Appr	-	-	-	Product family				D-SUB	Spec ref -		
		FEMALE CONNECTOR DELTA D					dwg no C01-8646-0431		Rev. E		
		with straight press fit contact									
		title		catalog no							CUSTOMER

rev	ecn no	dr	date
C	LS06-0011	MPE	2006/01/11
D	LS06-0097	LGO	2006/07/29
E	LS06-0140	LGO	2006/11/21
-	-	-	-
-	-	-	-
-	-	-	-

REV F - 2006-04-17

1

2

3

4



Copyright FCI.