molex



Part Number : 1300950142
Product Description : Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Standard Mesh Length 1.067m (42.00"), Approximate Break Strength 21772.43kg (48000 lbs)
Series Number : 130095
Status : Obsolete
Product Category : Cable Grips
Engineering Part Number : 35887

Documents and Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Obsolete

Downloaded from Arrow.com.

Part Details

General

Status	Obsolete
Category	Cable Grips
Series	130095
Description	Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Standard Mesh Length 1.067m (42.00"), Approximate Break Strength 21772.43kg (48000 lbs)
Product Name	Heavy Duty
Type	Pulling Grip
UPC	78678835887

Agency

CSA	LR32159

Physical

Approximate Break Strength	21772.43kg (48000 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	101.60-114.05mm (4.000-4.490")
Color - Grommet	N/A
Eye Diameter	1 7/8"
Eye Type	Rotating
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	1.067m (42.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

Obsolete

Downloaded from Arrow.com.