

ASSMANN
components

deutsch | english

Search:



The company | **Products** | Articlefinder | Contacts | Distribution | Download | Service

Connectors

- Customer specific solutions
- D SUB
- D SUB cover
- D SUB accessories
- DVI
- Centronics
- IDC
- Modular
- USB
- IEEE 1394
- Switches
- Power supply
- DIN 41612
- DIN 41617
- Mini DIN
- IC Socket
- **Pin and female header**
- Jumper
- Connector sleeves
- Solder terminals
- Test terminals
- Terminal Blocks
- Memory Card connectors
- FFC / FPC connectors
- Micro-Miniature



Pin and female header

AP 126-36/G-N
male-single-contact 14pins THT 2,54mm 3A on metal strips 7,43mm straight Au

Article number: APC 14 C

product group: pin-&female-header

style: male-single-contact

contact type: THT

pin count: 14

spacing in mm: 2,54

current rating: 3A

version: on metal strips

contact length: 7,43mm

contact direction: straight

plating: Au

contact machining: stamped contacts

packaging: polybag

process: THT

insulator: PBT UL94V-0

: AP 126-36/G-N

: #NV

» PDF download «

Thermal management

Cable assembly



