

[\(http://www.scansource.eu/\)](http://www.scansource.eu/)**Honeywell**<http://www.honeywellaidc.com/en-GB/Pages/default.aspx>[Promotions \(/promotions\)](#) [News \(/news\)](#) [Grow your Business \(/grow-your-business\)](#)[ps://europe.fastcatalog.net/](#)

Find Honeywell product info in one mouse click:

Datasheets, virtual tour, images, partnumbers, ...

Product Quickfinder ▼

[Home \(/\)](#) [Products \(/products\)](#) [Laser Scanners \(/products/laser-scanners\)](#) [Voyager 1202g Bluetooth](#)

Voyager 1202g Bluetooth

<http://honeywell.scansource-europe.com/sites/honeywell.scansource-europe.com/files/products/pictures>

Honeywell's Voyager™ 1202g single-line laser scanner incorporates the freedom of Bluetooth® wireless technology and offers a field-replaceable battery that can be quickly and easily exchanged. The new 1202g delivers the aggressive linear bar code scanning that users have come to expect from the world-renowned Voyager family of scanners.

Download



Select a datasheet ▼

Specifications

Bluetooth® Wireless Technology: Facilitates scanning of all standard 1D bar codes 10 meters (33 feet) or more away from the base, depending on the user's environment

Long Battery Life and Tool-Free Battery Removal: The user-preferred Lithium ion battery provides 12 hours or more of use, depending on scanning volume, and the field-replaceable battery can be exchanged quickly and easily, without the use of tools

Automatic Interface Configuration: Supports all popular interfaces in one device, replacing the time consuming process of scanning programming bar codes with automatic interface detection and configuration

Excellent Poor Quality Code Reading: Increases throughput and reduces the potential for hand-keyed errors by quickly scanning a variety of 1D bar codes, including those that are damaged or smudged

Paging Functionality: Simply press the button on the base to locate your lost scanner; Voyager 1202g responds with a series of beeps and blinking lights on its indicator panel

Remote MasterMind™ Ready: Reduces total cost of ownership by providing a turnkey remote device management solution that easily manages and tracks usage of installed devices

Kit

1202g-1USB-5 USB Kit: ivory BT 10m scanner (1202g-1), charge & communication base (CCB00-010BT-01N), USB Type A 3m straight cable (CBL-500-300-S00), and documentation

1202g-2USB-5 USB Kit: black BT 10m scanner (1202g-2), charge & communication base (CCB00-010BT-01N), USB Type A 3m straight cable (CBL-500-300-S00), and documentation

1202G-2USB-5BF USB Kit : Black BT 10m battery free scanner (1202g-2-BF), charge & communication base (CCB00-010BT-01N-BF), USB Type A 3m straight cable (CBL-500-300-S00), and documentation. Power Supply PS-05-1000W-X can be ordered separately

Scanner Only - cable sold separately

Power

Cables

Stands/Holders/Access Points

Service & Repair - Scanner Service Contracts

Sitemap

[Home \(/\)](#) [Products \(/products\)](#) [Promotions \(/promotions\)](#) [News \(/news\)](#)
[Grow your Business \(/grow-your-business\)](#) [Contact \(/contact\)](#)
[Order Now \(https://europe.fastcatalog.net/\)](https://europe.fastcatalog.net/)

[Scansource Europe \(http://www.scansource.eu/ \)](http://www.scansource.eu/)

[Honeywell \(http://www.honeywellaidc.com/en-GB/Pages/default.aspx\)](http://www.honeywellaidc.com/en-GB/Pages/default.aspx)

[Terms of Use \(/terms-use\)](#)

Webdesign

Cookie Control

This site uses cookies to store information on your computer.

[read more](#)

Contact

Call your local freephone number to get in touch with a ScanSource Europe Account Manager. Click the button below to find the overview of the available ScanSource Europe freephone numbers.

[Freephone numbers \(/contact\)](#)

© Copyright 2012 ScanSource Honeywell