Part Number : 2291132144
Product Description : Pre-Crimped Lead CP-3.3 Male-to-Pigtail, Tin (Sn) Plating, 300.00mm Length, 22 AWG, Black
Series Number : 229113
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

2291132144_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	229113
Description	Pre-Crimped Lead CP-3.3 Male-to-Pigtail, Tin (Sn) Plating, 300.00mm Length, 22 AWG, Black
Application	Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	CP-3.3 Crimp Terminals
Keyword	Pre-Crimped Leads
Product Name	CP-3.3
UPC	198930216629

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	300V AC (RMS)/DC

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Male-Pigtail
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.948/g
Packaging Type	Bag

Downloaded from Arrow.com.

Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1007
Wire Size (AWG)	22

Mates With / Use With

Use with Part(s)

Description	Part Number
CP-2.5 Mini Single Row Plug Housings	500593
CP-3.3 Single Row Plug Housings	504694
CP-3.3 Dual Row Plug Housings	505606

Downloaded from Arrow.com.