





© COPYRIGHT 1977 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

UNPUBLISHED COPY NOT TO BE
REPRODUCED NOR PUBLISHED
WITHOUT WRITTEN PERMISSION
OF AMP INCORPORATED.



					LOC	DIST
					2	37
REVISIONS						
P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
				SK-50858C	9-10-77	
				RELEASED FOR PROD.	9-10-77	
				ADDED NOTE 1 & MARKING ECN 8180	10-28-77	
		C-3	B	.400 WAS .370, .03 WAS .06, ECN 8192, DS	11-16-77	
			C	REV. PER ECN 8227	2-15-78	
			D	UP-DATED ECN 8384	9-6-78	
			E	OBSOLETE -5 ECN L1556	4-7-81	
				REACTIVATED -5 ECN S 3524		
F REV PER ECO-10-017059					12-10	DE

AMP P/N	CONTACT	"A" DIM.	"B" DIM.
863773-1	2	.375	.250
863773-2	4	.625	.500
863773-3	6	.875	.750
863773-4	8	1.125	1.000
863773-5	10	1.375	1.250
863773-6	12	1.625	1.500

1. LINE NUMBERS ARE MARKED ON THE SIDES COUNTING FROM 1 TO N AS SHOWN (N=NUMBER OF CONTACTS).

				PART NO	
				AMP INCORPORATED Elizabethtown, Pa.	
				NAME PIN HOUSING ASSEMBLY	
				SIZE CODE IDENT NO DRAWING NO C 00779 863773	
				SCALE ~ SHEET 1 OF 1 REV F	
				CUSTOMER DRAWING	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES: .00 ± .02, .000 ± .005 ANGLES ±				CONTRACT NO 8-3-77	
MATERIAL MOLDED GLASS EPOXY				APPD 8-3-77	
FINISH BLACK				APPD 9-21-77	
NEXT ASSY				DSGN APPD	
QTY REQD				OTHER APPD	
APPLICATION					