

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936014694

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

Gwconnect STD - Standard S-CX/3A Shielded Circular BUS Connector, Male, 4-Pole, with Size 3A «21x21» Hood, with Gasket, Pg11/Pg13.5, Black

Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Comments	Contacts to be ordered Separately.
Component Size	3A «21x21»
Component Type	Circular BUS Connector
IP Rating	IP66, IP67
Insert Series	S-CX
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	EN 60664-1, EN 61984, UL 1977
Taxonomy	Heavy-Duty Connectors
Type	STD
UPC	887191843322
Physical	
Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Male
Hood Coating	Polyester Powder
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Gasket	NBR
Material - Hood	Die-cast Aluminum
Material - Insert	Polycarbonate
Material - Peg	Die-cast Aluminum
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	4
Temperature Range - Operating	-40° to +125°C
Thread Size	Pg11, Pg13.5
Thread Type	(Pg)
Electrical	
Current - Maximum per Contact	10.0A
Voltage	EN 61984: 50V 0.8kV 3
Material Info	
Engineering Number	7913.3496.0



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

93601 Series

Mates With

93601-4634 Female Circular BUS Connector Housing Assembly

Use With

S-D Series Male Turned Crimp Contact

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION