

[Skip Navigation](#)

[TE Connectivity](#)

© 2019 TE Connectivity Ltd. family of companies. All Rights Reserved

This product is not currently available. For more information, including distributor inventory, please [contact us](#).

- Antennas
- Antennas
- Application Tooling
- Application Tooling
- Splices
- Cable Assemblies
- PIDG BUTT SPLICES
- Connectors
- Connectors
- EMI Filters
- EMI Filters
- Fiber Optics
- Fiber Optics
- Harnessing
- Harnessing
- Heat Shrink Tubing
- Heat Shrink Tubing
- Identification & Labeling
- Identification & Labeling
- Passive Components
- Passive Components
- Power Systems
- Power Systems
- Relays, Contactors & Switches
- Relays, Contactors & Switches
- Sensors
- PIDG Sensors
- Terminals & Splices
- Terminals & Splices
- Wire & Cable
- Wire & Cable

SPLICE BUTT PIDG 24-20

SPLICE BUTT PIDG 24-20-323975

- Heat Shrink Tubing
- Heat Shrink Tubing
- Identification & Labeling
- Identification & Labeling
- Passive Components
- Passive Components
- Power Systems
- Power Systems
- Relays, Contactors & Switches
- Relays, Contactors & Switches
- Sensors
- PIDG Sensors
- Terminals & Splices
- Terminals & Splices
- Wire & Cable
- Wire & Cable

SPLICE BUTT PIDG 24-20

- TE Internal #. 323975
- TE Internal Description: SPLICE BUTT PIDG 24-20
- Mil-Spec: M7928/5-2
- All PIDG BUTT SPLICES (29)
- Wire & Cable
- Wire & Cable

Product Type: Splice

Terminal & Splice Type : Splice

Wire Size (AWG): 24 - 20

Wire Size (mm²): .2 - .6

Sealable : No

[See All Features](#)

[More Less](#)

- ENTRELEC
- Hartman
- HIRSCHMANN MOBILITY
- Intersontec
- Kilovac
- Madison Cable
- Measurement Specialties
- Microdot
- Compatible Parts & Tooling
- Potter & Brumfield
- Raychem
- Schrack

Free Shipping

to select countries. Exclusions apply. See complete details at [TE Store FAQs](#)

Downloaded from [Arrow.com](#)

Feedback

- Industries & Solutions
- QTY:
- Extended Price:
- Contact Us
- Automotive
- Autosport
- Communications & Wireless Equipment
- Connected Home
- Consumer Solutions
- Data Centers
- Defense & Military
- Energy & Utilities
- Hybrid & Electric Mobility
- Industrial Machinery
- Intelligent Buildings
- Medical & Healthcare
- Oil & Gas / Marine
- Sensor Solutions
- Truck, Bus & Off-Road Vehicles

We are here to help!

Get in touch with our product experts.

Chat with us

- Documents
- Features
- Product Compliance

Documents

Products with Similar Specs

Product Description

THIS PRODUCT IS THE INTERNET OF THINGS (IOT)

Pre-Insulated Diamond Grip Butt Splices [View All PIDG BUTT SPLICES \(29\)](#)

Splices [Electric Vehicles and Connected Transportation](#)

Product Drawings and Digital Production

323975 [Smart Connectivity for Smart Cities](#)

[SPICE BUTT PIDG 12-10](#) [SPICE BUTT PIDG 24-20](#) English

[SPLICE BUTT PIDG 24-20](#) [Materials Science, 3D Printing, & Digital Manufacturing](#)

CAD Files

[TE.com Store](#)

From 3D PDF to thousands of products available with same-day shipping.

[Customer View Model ENG_CVM_323975_M.2d_dxf.zip](#) English

In-Stock [ENG_Review three samples of TE products](#)

[ENG_Compare Products 3d_stp.zip](#) English

Product Type: Splice

Terminal & Splice Type

Splice [Save preferred products you can export and share](#)

Wire Size: 24 – 20 AWG

PIDG Terminal Splice SPLICES Quick Reference Guide [ENG_DS_1773464-1_ORG_PIDG_1901.pdf](#) English

Wire Size: 2 – 6 mm²

Scalable: No

Product Specifications

[Distributor Inventory](#)

TOP RESULTS [Application Specification Reference SS_114-2157_G.pdf](#) English

Splices [Track Order History](#)

Product Environmental Compliance

[2-32397593 Electrical Models](#)

[Management System Certification 323975_AA.pdf](#) English

[SPLICE BUTT PIDG 24-20; TAPE](#)

[View All Resources](#)

Agency Approvals

[TE Store](#)

From UL Report [ENG_AAD_UL_E13288_19791001_B.pdf](#) English

In-Stock [CSA Certificate ENG_AAD_CSA_164196_6223_1693113_A.pdf](#) English

[Hi, GivenName](#)

[Product Type: Splice](#)

Terminal & Splice Type :

Product Splice

Product Description

[Car](#) Wire Size : 24 – 20 AWG

Wire Size : 2 – 6 mm²

Pre-Insulated Diamond Grip Butt Splices [View All PIDG BUTT SPLICES \(29\)](#)

Scalable: No

Please review product documents or [contact us](#) for the latest agency approval information.

Splices [Resources](#)

[TE Store](#)

[320570](#) [Cart \(0\)](#)

Please Note: Use the Product Drawing for all design activity.

[SPLICE BUTT PIDG 12-10](#)

[Sign In](#)

[Live Chat](#)

Product Type Features

Products From [n. Product Type : Splice](#)

Industries & Solutions

In-Stock [Scalable: No](#)

Downloaded from [Arrow.com](#)

Resources
Product Type : **Splice**
MY Terminal & Splice Type : **Splice**

- **Splice Type : *Butt Splice***
 - **Sealable : *Yes***
 - Wire Size : 12 – 14 AWG
 - Wire Size : 3 – 6 mm²
- Our website has detected that you are using an unsupported browser that will prevent you from accessing certain features.

We strongly recommend that you upgrade to the most recent version of your browser.

Splices
• **Support Style : *Insulation Support***

Due to scheduled maintenance, some services are not functioning on TE.com We expect everything to be up by 4:30pm EST / 3:30pm CST. Thanks for your patience.

Body Features

SPLICE BUTT PIDG 16-14

Welcome to TE.com, you are viewing information for visitors in United States

• **Splice Material : *Copper***

CHOOSE ANOTHER SITE STAY ON THIS SITE

From
• **Color : *Natural - Translucent***

Contact Features

- Product Type & Splice Type : **Terminal & Splice Type : *Splice***
- Terminal & Splice Type :

Dimensions

- Wire Size : 16 – 14 AWG
- Wire Size : 1.25 – 2 mm²
- **Wire Size (AWG): *24 – 20***
- Sealable : No

[View Wire Size \(mm²\): .2 – .6](#)

These options have been chosen from a pool of Terminals & Splices with similar specs to this product.

Also in the Series: [PIDG 1290](#)

Industry Standards
[Compression Connectors-42630](#)

- **Government Qualified : *Yes***
- [Crimp Terminal Housings-42766](#)

Packaging Features
[Crimp Terminal Housings \(1\)](#)

-  **Piece**

Product

State

- [Statement of Compliance.pdf](#)
- [Crimp Wire Pins, Tabs & Ferrules \(41\)](#)



- [Knife Disconnects \(11\)](#)

- [PCB Terminals-42760](#)

[PCB Terminals \(9\)](#)

- [Portable Crimp Tools-41510](#)

[Portable Crimp Tools \(1\)](#)

- [Quick Disconnects-546246](#)

[Quick Disconnects \(53\)](#)

- [Rings & Spades-546245](#)

[Rings & Spades \(862\)](#)

- [Special Purpose Terminals-42762](#)

[Special Purpose Terminals \(1\)](#)

Need help?

Our team is on stand-by and ready to help with your order.

[CHAT NOW](#)

Terms and Conditions

- [I Agree](#)
- [I Disagree](#)

[Call Us](#)

[Live Chat](#)

- **[About TE Connectivity](#)**

- [Our Company](#)
- [Events](#)
- [TE News Center](#)
- [Careers](#)
- [Investors](#)
- [Corporate Responsibility](#)

- **[For Partners](#)**

- [Distributors](#)
- [Suppliers](#)

- **[Support](#)**

- [Customer Service](#)
- [Find Authorized Distributors](#)
- [TE Store FAQs](#)
- [Product FAQs](#)
- [Terms and Conditions of Sale](#)

- [Call Us](#)

- [Live Chat](#)

- [Contact Us](#)

- **Change Country & Language**

[United States \(EN\)](#)

- Select Country & Language
- [United States \(EN\)](#)
- [Germany \(DE\)](#)
- [China \(中文\)](#)
- [Japan \(日本語\)](#)

Find Your Country/Region

- [Afghanistan \(EN\)](#)
- [Albania \(EN\)](#)
- [Algeria \(EN\)](#)
- [American Samoa \(EN\)](#)
- [Andorra \(EN\)](#)
- [Angola \(EN\)](#)
- [Anguilla \(EN\)](#)
- [Antarctica \(EN\)](#)
- [Antigua and Barbuda \(EN\)](#)
- [Argentina \(EN\)](#)
- [Armenia \(EN\)](#)
- [Aruba \(EN\)](#)
- [Australia \(EN\)](#)
- [Austria \(EN\)](#)

- Bahamas (EN)
- Bahrain (EN)
- Bangladesh (EN)
- Barbados (EN)
- Belarus (EN)
- Belgium (EN)
- Belize (EN)
- Benin (EN)
- Bermuda (EN)
- Bhutan (EN)
- Bolivia (EN)
- Bonaire (EN)
- Bosnia and Herzegovina (EN)
- Botswana (EN)
- Bouvet Island (EN)
- Brazil (EN)
- British Indian Ocean Territory (EN)
- British Virgin Islands (EN)
- Brunei Darussalam (EN)
- Bulgaria (EN)
- Burkina Faso (EN)
- Burundi (EN)
- Cabo Verde (EN)
- Cambodia (EN)
- Cameroon (EN)
- Canada (EN)
- Cayman Islands (EN)
- Central African Republic (EN)
- Chad (EN)
- Chile (EN)
- China (中文)
- China Hong Kong (EN)
- China Macau (EN)
- China Taiwan (EN)
- Christmas Island (EN)
- Cocos (Keeling) Islands (EN)
- Colombia (EN)
- Comoros (EN)
- Congo (EN)
- Cook Islands (EN)
- Costa Rica (EN)
- Croatia (EN)
- Curaçao (EN)
- Cyprus (EN)
- Czech Republic (EN)
- Côte d'Ivoire (EN)
- Democratic Republic of the Congo (EN)
- Denmark (EN)
- Djibouti (EN)
- Dominica (EN)
- Dominican Republic (EN)
- Ecuador (EN)
- Egypt (EN)
- El Salvador (EN)
- Equatorial Guinea (EN)
- Eritrea (EN)
- Estonia (EN)
- Ethiopia (EN)
- Falkland Islands (EN)
- Faroe Islands (EN)
- Fiji (EN)
- Finland (EN)
- France (EN)
- French Guiana (EN)
- French Polynesia (EN)
- French Southern Territories (EN)
- Gabon (EN)
- Gambia (EN)
- Georgia (EN)
- Germany (DE)
- Ghana (EN)
- Gibraltar (EN)

- Greece (EN)
- Greenland (EN)
- Grenada (EN)
- Guadeloupe (EN)
- Guam (EN)
- Guatemala (EN)
- Guernsey (EN)
- Guinea (EN)
- Guinea-Bissau (EN)
- Guyana (EN)
- Haiti (EN)
- Heard Island and McDonald Islands (EN)
- Honduras (EN)
- Hungary (EN)
- Iceland (EN)
- India (EN)
- Indonesia (EN)
- Iraq (EN)
- Ireland (EN)
- Isle of Man (EN)
- Israel (EN)
- Italy (EN)
- Jamaica (EN)
- Japan (日本語)
- Jersey (EN)
- Jordan (EN)
- Kazakhstan (EN)
- Kenya (EN)
- Kiribati (EN)
- Kuwait (EN)
- Kyrgyzstan (EN)
- Laos (EN)
- Latvia (EN)
- Lebanon (EN)
- Lesotho (EN)
- Liberia (EN)
- Libya (EN)
- Liechtenstein (EN)
- Lithuania (EN)
- Luxembourg (EN)
- Macedonia (EN)
- Madagascar (EN)
- Malawi (EN)
- Malaysia (EN)
- Maldives (EN)
- Mali (EN)
- Malta (EN)
- Marshall Islands (EN)
- Martinique (EN)
- Mauritania (EN)
- Mauritius (EN)
- Mayotte (EN)
- Mexico (EN)
- Micronesia (EN)
- Moldova (EN)
- Monaco (EN)
- Mongolia (EN)
- Montenegro (EN)
- Montserrat (EN)
- Morocco (EN)
- Mozambique (EN)
- Myanmar (EN)
- Namibia (EN)
- Nauru (EN)
- Nepal (EN)
- Netherlands (EN)
- New Caledonia (EN)
- New Zealand (EN)
- Nicaragua (EN)
- Niger (EN)
- Nigeria (EN)
- Niue (EN)

- Norfolk Island (EN)
- Northern Mariana Islands (EN)
- Norway (EN)
- Oman (EN)
- Pakistan (EN)
- Palau (EN)
- Palestine (EN)
- Panama (EN)
- Papua New Guinea (EN)
- Paraguay (EN)
- Peru (EN)
- Philippines (EN)
- Pitcairn (EN)
- Poland (EN)
- Portugal (EN)
- Puerto Rico (EN)
- Qatar (EN)
- Romania (EN)
- Russia (EN)
- Rwanda (EN)
- Réunion (EN)
- Saint Barthélemy (EN)
- Saint Helena, Ascension and Tristan da Cunha (EN)
- Saint Kitts and Nevis (EN)
- Saint Lucia (EN)
- Saint Martin (EN)
- Saint Pierre and Miquelon (EN)
- Saint Vincent and the Grenadines (EN)
- Samoa (EN)
- San Marino (EN)
- Sao Tome and Principe (EN)
- Saudi Arabia (EN)
- Senegal (EN)
- Serbia (EN)
- Seychelles (EN)
- Sierra Leone (EN)
- Singapore (EN)
- Sint Maarten (EN)
- Slovakia (EN)
- Slovenia (EN)
- Solomon Islands (EN)
- Somalia (EN)
- South Africa (EN)
- South Georgia and the South Sandwich Islands (EN)
- South Korea (EN)
- Spain (EN)
- Sri Lanka (EN)
- Suriname (EN)
- Svalbard and Jan Mayen (EN)
- Swaziland (EN)
- Sweden (EN)
- Switzerland (EN)
- Tajikistan (EN)
- Tanzania (EN)
- Thailand (EN)
- Timor-Leste (EN)
- Togo (EN)
- Tokelau (EN)
- Tonga (EN)
- Trinidad and Tobago (EN)
- Tunisia (EN)
- Turkey (EN)
- Turkmenistan (EN)
- Turks and Caicos Islands (EN)
- Tuvalu (EN)
- U.S. Virgin Islands (EN)
- Uganda (EN)
- Ukraine (EN)
- United Arab Emirates (EN)
- United Kingdom (EN)
- United States (EN)
- United States Minor Outlying Islands (EN)

- Uruguay (EN)
- Uzbekistan (EN)
- Vanuatu (EN)
- Vatican City (EN)
- Venezuela (EN)
- Vietnam (EN)
- Wallis and Futuna (EN)
- Western Sahara (EN)
- Yemen (EN)
- Zambia (EN)
- Zimbabwe (EN)
- Åland Islands (EN)

- [Terms of Use](#)
- [Privacy](#)
- [Cookie Policy](#)
- [Accessibility](#)
- [Site Map](#)

- © 2019 TE Connectivity. All Rights Reserved.

- [Facebook](#)
- [Twitter](#)
- [LinkedIn](#)
- [YouTube](#)
- [Instagram](#)

- [Facebook](#)
- [Twitter](#)
- [LinkedIn](#)
- [YouTube](#)
- [Instagram](#)

© 2019 TE Connectivity. All Rights Reserved.

View this page on [TE mobile site](#).