



Part Number : [1300000076](#)

Product Description : Quick-Change Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 14 AWG, Yellow CPE Cable, 3.66m (12.0') Length

Series Number : 130000

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 32639


Documents and Resources

Drawings

[1300000076 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[UKCA - Declaration of Conformity](#)

[CE - Declaration of Conformity](#)

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130000
Description	Quick-Change Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 14 AWG, Yellow CPE Cable, 3.66m (12.0') Length
IP Rating	IP67
Product Name	Quick-Change
Type	Single Ended
UPC	78678832639

Agency

CSA	LR6837
UL	E46237

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	600V

Physical

Cable Diameter	15.74mm (.620")
Cable Length	3.66m (12.0')
Color - Cable Jacket	Yellow
Connector End A	Quick-Change
Connector End B	Pigtail
Coupling Style	Threaded

Gender	Female-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	CPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Nylon
Material - Plating Mating	N/A
Net Weight	477.000/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	SOW
Wire Size (AWG)	14

This document was generated on May 26, 2026