Part Number : 191600190
Product Description : Closed-End Insulated Splice for 18-10 AWG Wire
Series Number : 19160
Status : Active
Product Category : Splices
Engineering Part Number : NC-1810



Documents and Resources

Drawings

191600190_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Splices
Series	19160
Description	Closed-End Insulated Splice for 18-10 AWG Wire
Product Name	Closed-End Insulated
Style	Standard
Type	Closed-end Connector
UPC	756054754405

Electrical

Voltage - Maximum	600V

Physical

Barrel Type	Closed
Color - Resin	Natural
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.236/g
Packaging Type	Carton
Temperature Range - Operating	-10° to +105°C
Wire Insulation Diameter	7.39mm max.

Downloaded from Arrow.com.

Wire Size (AWG)	10, 12, 14, 16, 18
Wire Size mm^2	0.823-5.26

Downloaded from Arrow.com.