


MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH — BASIC

CATALOG LISTING
BZ-3RW80552-A2-S



NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .165 MAX DIA ON 1.000 ± .002 CENTERS
- 2 - SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS

OPERATING FORCE ——— 4 OZ MAX
RELEASE FORCE ——— 3/4 OZ MIN
DIFFERENTIAL TRAVEL ——— .010—.060
OVERTRAVEL ——— .172 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L96 15A 125, 250 OR 480 VAC
1/8 HP 125 VAC, 1/4 HP 250 VAC
1/2A 125 VDC, 1/4A 250 VDC

L288
L299
L306

CE D RU S
16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE 2

	DES. UNITS	TOL. IN	TOL. MM
NO PLACES	X	1/64	0.015
ONE PLACE	X.X	0.0010	0.025
TWO PLACES	X.XX	0.0005	0.0125
THREE PLACES	X.XXX	0.0002	0.005

DESIGN UNITS ☐ METRIC ☐ US CUSTOMARY

WEIGHT .076 LB

M BZ-3RW80552-A2-S

DRAWING NUMBER

5

ISSUE

REPLACES

PR-14831

PAGE 1 OF 1

CHECK

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

17

18

FORMTEK

FO-52848-A

DRAWN

J A P 17 JUN 86

CHECKED

9 JUN 86

19