


ALL DIMENSIONS ARE FOR REFERENCE ONLY

DO NOT SCALE DRAWING

ALL DIMENSIONS IN mm UNLESS STATED.

OPERATING CRITERIA

VOLTS; 240VAC

AMPS; 10A

OPERATING CRITERIAOPEN; $100 \pm 4^{\circ}\text{C}$ CLOSE; $85 \pm 5^{\circ}\text{C}$ SPECIAL ARRANGEMENTS


PURPLE SPOT

NOTE:-

CODING TO SUIT MANUFACTURING SITE

6.35 X 0.8 Q.C.

6.35 X 0.8 Q.C.



NOTE:- ORIENTATION OF BRACKET IS NOT FIXED

DRAWN BY;

G.D.

ISSUE
MOD No.
MTH/YRA
3052
03/97B
3358
07/98C
3640
01/01CODING REQUIREMENTS

COLOUR; WHITE

L100C

9100-438-UXX

7100-438-ZXX

(XXX = DATE CODING)

CAP;

MAT'L;

BRK'T;

B203S

MAT'L;

STEEL

PLATING;

NICKEL

TERMINAL;

T146

MATERIAL;

BRASS

PLATING;

-

ELMWOOD DEVICE & UNIQUE PART NUMBER

2455RP-9100-438(UK)

2455RP-7100-438(CHINA)

DATE OF ISSUE STAMP

18 JAN 2001

ELMWOOD DRG No.

965206

ISSUE

C