

40Gb Pass-Through Cassette - (x6) 12-Fiber MTP/MPO (Female)

MODEL NUMBER: **N482-6M12-6M12**



Description

Tripp Lite's N482-6M12-6M12 is a High Density 40Gb Pass-through Cassette, with (x6) 12-Fiber MTP/MPO connections. For use with Tripp Lite's N482-01U and N482-02U High Density Fiber Enclosure Panels; up to 5 cassettes per N482-01U, or up to 14 cassettes per N482-02U. Guaranteed compatibility when used with recommended Tripp Lite cabling. Designed specifically for use with Tripp Lite cables, such as the N842-, N844- and N845-Series cables. Installation is simple, with the cassette being easily installed or removed using push / pull tabs to lock or unlock it from the panel; no tools required. Furthermore, each cassette features factory terminated connectors that reduce the time and labor required of field connector terminations.

Features

- High Density Fiber Cassette for use with Tripp Lite N482-01U and N482-02U High Density Fiber Enclosure Panels
- 40Gb Pass-through Cassette, with (x6) 12-Fiber MTP/MPO connections
- Guaranteed compatibility when used with recommended Tripp Lite cabling
- Designed specifically for use with Tripp Lite cables, such as the N842-, N844- and N845-Series cables
- Installation is simple, with the cassette being easily installed or removed using push / pull tabs to lock or unlock it from the panel; no tools required.
- Factory terminated connectors reduce the time and labor required of field connector terminations

Specifications

OVERVIEW	
UPC Code	037332184573
Technology	Multimode

Highlights

- High Density Fiber Cassette for use with Tripp Lite N482-01U and N482-02U High Density Fiber Enclosure Panels
- 40Gb Pass-through Cassette, with (x6) 12-Fiber MTP/MPO connections (Female)
- Guaranteed compatibility when used with recommended Tripp Lite cabling
- Designed specifically for use with Tripp Lite cables, such as the N842-, N844- and N845-Series cables
- Factory terminated connectors reduce the time and labor required of field connector terminations

System Requirements

- Guaranteed compatibility when used with recommended Tripp Lite cabling
- Designed specifically for use with Tripp Lite cables, such as the N842-, N844- and N845-Series cables

Package Includes

- N482-6M12-6M12 40Gb Pass-through Cassette - (x6) 12-Fiber MTP/MPO
- Quick Start Guide

PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	2.40 x 4.10 x 2.40
Shipping Dimensions (hwd / cm)	6.10 x 10.41 x 6.10
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
Unit Dimensions (hwd / in.)	1.200 x 3.500 x 0.900
Unit Dimensions (hwd / cm)	3.05 x 8.89 x 2.29
Unit Weight (lbs.)	0.18
Unit Weight (kg)	0.08
CONNECTIONS	
Number of Ports	6
Side A - Connector 1	12-STRAND MTP/MPO (FEMALE)
Side B - Connector 1	12-STRAND MTP/MPO (FEMALE)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty