










Verpackt im Gurt in Anlehnung an DIN IEC 60286-3
tape on reel packaging according to DIN IEC 60286-3
 Verpackungseinheit: 380 Stück
packaging unit: 380 pcs







Abspulrichtung - *reel off direction*



Leiterplatten-Layout Vorschlag für SMT
PCB-Layout Proposal for SMT




474019-E		rot red	3,9	0,9	4,5	0,3	
474018-E		grün green	2,7	2,1	3,3	1,5	
474017-E		blau blue	1,5	3,3	2,1	2,7	
474016-E		schwarz black	0,3	4,5	0,9	3,9	
Ident-Nr. part-no.	Codierung coding	Farbe color	A	B	C	D	Bemerkung note

Anforderungsstufe 1
performance level 1

Kontaktbereich vergoldet
mating area gold plating

Anschlussbereich verzinnt 4-6 µm
terminal area 4-6 µm tin plating

Koplanarität der Anschlüsse $\leq 0,1 \text{ mm}$
coplanarity area of termination $\leq 0,1 \text{ mm}$

Dimension no.				Tolerances Dim. for Information ISO 8015		 All Dimensions in mm		Scale 3:1			
Customer drawing: THIS DRAWING IS A CONTROLLED DOCUMENT.				Subject to modification without prior notice. Drawing will not be updated.				ERNI-M 2,54 DRC-B, 10-polig			
b				21.10.2015				C- 324229-E			I
Index				Date				Class DRCB			A3