

AMD

Enabling today.
Inspiring tomorrow.

SHOP AMD HOME / SELECT COUNTRY

SHOP MANUFACTURERS / SHOP RETAILERS

SEARCH SHOP AMD

All

FOLLOW US

f

t

in

g+

p

SHOP COMPUTERS

SHOP COMPONENTS

HOME

GAMING

BUSINESS

Shop AMD > Processors > AMD Quad-Core A8-Series APU A8-6600K with Radeon HD 8570D (AD660KWOHLBOX)

Shop AMD



AMD Quad-Core A8-Series APU A8-6600K with Radeon HD 8570D (AD660KWOHLBOX)

★★★★★ (50 reviews)

CPU Model: A8-6600K with Radeon™ HD 8570D

CPU Line: AMD Quad-Core A8-Series APU for Desktops

Frequency: 3900

Socket Type: FM2

Power Wattage: 100

plus shipping¹

7 SELLER(S)

View Systems with AMD Quad-Core A8-Series APU A8-6600K with Radeon HD 8570D (AD660KWOHLBOX)



iBuyPower (ecx-Tig-US-11B-102352350) AMD Quad-Core A8-Series APU with AMD Radeon R9 260X HD 1TB RAM 8GB Windows 8.1

> View All Systems with this component

Similar Products



AMD Quad-Core A8-Series APU A8-5500 with Radeon HD 7560D (AD5500KA44HJ)



★★★★★
AMD Quad-Core A8-Series APU A8-5600K with Radeon HD 7560D (AD560KWOHJBOX)

> View All Similar Products

COMPARE PRICES	DETAILS	RATINGS AND REVIEWS
	Amazon-US	plus shipping ¹ LOW
	NCIX-US	plus shipping ¹ LOW
	Newegg Business	plus shipping ¹ LOW
	Fry's-US	plus shipping ¹ LOW
	Microcenter-US	plus shipping ¹ LOW
	Newegg-US	plus shipping ¹ LOW
	TigerDirect	plus shipping ¹ LOW
Price		
Best Price:		
Description		
Processor Type:	AMD Quad-Core A8-Series APU for Desktops	
Model:	A8-6600K with Radeon™ HD 8570D	
Part Number:	AD660KWOHLBOX	
Socket Type:	FM2	

Power Wattage:	100
Frequency:	3900
Processor Bus Speed:	Not Specified
Processor L2 Cache Size:	4096
CMOS:	32nm SOI
Stepping:	Not Specified
Fusion Control Hubs:	Not Specified
Direct X Version:	11
GPU Clock Speed:	844

¹AMD is not responsible for typographical or photographic errors, or ratings and reviews, which are provided for informational purposes only. Price and specifications are subject to change without notice and may vary from what is listed on the vendor website.