

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190110037

Status:

Active

Overview:

Standard Quick-Disconnect Terminals

Description:

InsulKrimp Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 14-16 AWG, Blue Insulator, Loose



Series image - Reference only

Documents:	
3D Model (PDF)	Product Specification PS-19902-011-001 (PDF)
3D Model	Product Specification PS-19902-013-001 (PDF)
Drawing (PDF)	Packaging Specification PK-19902-001-001 (PDF)
Product Specification PS-19902-008-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR18689
UL	E79133
General	
Product Family	Quick Disconnects
Series	19011
Crimp Quality Equipment	Yes
Insulated	Partial
Overview	Standard Quick-Disconnect Terminals
Product Name	InsulKrimp
Type	Quick Disconnect
UPC	822350942447
Physical	
Barrel Type	Closed
Color - Resin	Blue
Flammability	94V-0
Gender	Female
Glow-Wire Capable	No
Insulation	PVC
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.078/g
Orientation	Straight
Packaging Type	Bag
Polarized to Mating Part	Yes
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	105°C
Wire Insulation Diameter	3.56mm max.
Wire Size AWG	14, 16
Wire Size mm²	1.30-2.00
Electrical	
Voltage - Maximum	600V AC
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	BB-2302
Reference - Drawing Numbers	

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

19011 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	640016200
Air Powered Crimp Tool Head	640056200

Packaging Specification
Product Specification

Sales Drawing

PK-19902-001-001
PS-19902-008-001, PS-19902-011-001,
PS-19902-013-001
SD-19011-004-001

This document was generated on 10/22/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION