



Have a Question?
Chat with a Product
Information Specialist

What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

[Home](#) > [Products](#) > [Input/Output \(Box to Box\)](#) > [Product Feature Selector](#) > Product Details

1-2132403-5 Product Details

Share Print Email

Pluggable Connectors, Cages & Accessories

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- SFP+ Product Line
- Cage Assembly with Integrated Connector
- SFP+ Enhanced EMI Application
- Connector Style = Receptacle
- Cage Type = Stacked

[View all Features](#)

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

[Feedback](#)

TE Internal Number: 1-2132403-5

Active

View 3D PDF

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information	
Product Drawings: CAGE AND PT CONNECTOR ASSEMBLY, WITH EMI SPRINGS, PR... (PDF, English) Catalog Pages/Data Sheets: - None Available Product Specifications: SFP+ Stacked Connector and Cage Assemblies (PDF, English) Application Specifications: Stacked Small Form-Factor Pluggable (SFP+) Connector... (PDF, English) Instruction Sheets: Small Form-Factor Pluggable (SFP)+ zSFP+ Extraction ... (PDF, English) Small Form-Factor Pluggable (SFP)+ Seating Tool Kits... (PDF, English) CAD Files: (CAD Format & Compression Information) 2D Drawing (DXF, Version A) 3D Model (IGES, Version A) 3D Model (STEP, Version A) List all Documents	Related Products: Tooling
Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: - Product Line = SFP+ - Product Type = Cage Assembly with Integrated Connector Mechanical Attachment: - PCB Mount = Single Sided Electrical Characteristics: - Data Signal Rate (Gb/s) = Up to 16 Termination Features: - Termination Method to PC Board = Through Hole - Press Fit Dimensions: - Tail Length (mm [in]) = 3 [0.118] - PCB Thickness, Recommended (mm [in]) = 1.50 [0.059] - Length (X-Axis) (mm [in]) = 64.25 [2.529] - Width (Z-Axis) (mm [in]) = 71.66 [2.821] - Profile Height (Y-Axis) (mm [in]) = 25.50 [1.0039] Body Features: - Integrated Light Pipes = Yes Contact Features: Contact Plating, Mating Area, Material = Gold or Gold Flash over Palladium Nickel - Contact Base Material = Copper Alloy Housing Features: - Connector Style = Receptacle Cage Type = Stacked - Housing Material = Liquid Crystal Polymer (LCP) - Housing Color = Black - Cage Material = Nickel Silver	Configuration Features: - Port Configuration = 2x5 - Lightpipe = With - Lightpipe Configuration = All Four - EMI Containment = External Springs Industry Standards: RoHS/ELV Compliance = RoHS compliant, ELV compliant Lead Free Solder Processes = Not relevant for lead free process - RoHS/ELV Compliance History = Always was RoHS compliant - UL Flammability Rating = UL 94V-0 Conditions for Usage: - Applies To = Printed Circuit Board Operation/Application: Application = SFP+ Enhanced EMI - Heat Sink Application = No Packaging Features: - Packaging Method = Box/Carton Other: - Brand = TE Connectivity