



NC4FD-L-BAG-1

4 pole female receptacle, solder cups, black metal housing, silver contacts

Universal D-size metal body XLR panel mount series. UL recognized component.

Features & Benefits

- ✓ Robust "D" metal shell
- ✓ Standardized D sized 24 mm panel cutout
- ✓ Solder cups on 3 - 7 pole version

Technical Information

Product	
Title	NC4FD-L-BAG-1
Connection Type	XLR
Gender	female

Electrical

Capacitance between contacts	$\leq 7 \text{ pF}$
Contact resistance	$\leq 5 \text{ m}\Omega$
Dielectric strength	1,5 kVdc
Insulation resistance	$> 10 \text{ G}\Omega$ (initial)
Rated current per contact	10 A
Rated voltage	$< 50 \text{ V}$

Mechanical

Insertion force	$\leq 20 \text{ N}$
Withdrawal force	$\leq 20 \text{ N}$
Lifetime	> 1000 mating cycles
Wiresize	max. 1.5 mm^2
Wiresize	max. 16 AWG
Wiring	Solder contacts
Locking device	Latch lock
Chassis shape	D

Material	
Contact plating	2 µm Ag over 2 µm Ni
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA66)
Locking element	Steel Ck67
Locking element plating	Nickel
Shell	Zinc diecast (ZnAl4Cu1)
Shell coating	Black KTL

Environmental	
Approvals	UL
Flammability	UL 94 V-0
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C