



Part Number : [1301120258](#)
Product Description : Replacement Guard for 5030,
10 Pack
Series Number : 130112
Status : Active
Product Category : Portable Lighting Accessories
Engineering Number : STR105



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Reviewed per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Portable Lighting Accessories
Series	130112
Description	Replacement Guard for 5030, 10 Pack
NEMA Configuration	N/A
Product Name	Woodhead
Type	Accessory
UPC	78172538191

Electrical

Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage (Fixture) - Maximum	N/A

Physical

Bulb Type	N/A
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	138.43mm (5.450")
Duty	Commercial
Guard Included	Yes
Guard Type	Polypropylene
Height	180.98mm (7.125")
Lamp Type	A21
Length	N/A
Material - Guard	Polypropylene
Outlet	N/A
Packaging Type	Carton

This document was generated on Sep 25, 2025