HellermannTyton

Specification Sheet

Part Number: TM1SF10M4



Push Mounts, when used with standard cable ties, provide a permanent bundling solution.

The low profile style head is ideal for space constrained areas and is easily inserted through a pre-drilled hole.

Push-Button Cable Tie Mount, 0.25" Hole Dia, 0.13" Max Panel, 0.2" Max Tie Width, PA66, White, 1000/pkg

Article Number	151-00328
Type	TM1SF
Color	White (WH)
Quantity Per	pack
Product Description	HellermannTyton push mounts are used with our standard cable ties and offer a permanent bundling solution for quick installation by pushing the mount through a pre-drilled hole. The low profile head is suitable in space constrained areas.
Short Description	Push-Button Cable Tie Mount, 0.25" Hole Dia, 0.13" Max Panel, 0.2" Max Tie Width, PA66, White, 1000/pkg
Global Part Name	TM1SF-PA66-WH

Downloaded from Arrow.com.

Length L (Imperial)	0.4
Length L (Metric)	10.2
Fixation Method	Arrowhead
Width W (Imperial)	0.3
Width W (Metric)	7.6
Cable Ties	T18 - T50
Height H (Imperial)	0.61
Height H (Metric)	15.6
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.0
Panel Thickness Min (Metric)	3.40
Panel Thickness Max (Metric)	3.40
Mounting Hole Diameter D (Imperial)	0.25 "
Mounting Hole Diameter D (Metric)	6.3 mm
Mounting Hole Diameter D Max (Metric)	6.35

Downloaded from Arrow.com.

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes

Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.