



**Part Number :** [1210120009](#)  
**Product Description :** mPm DIN Base, Form B-11mm, B15 Base, 2 Pole Plus Ground Terminal, 250V AC/300V DC, Black, Nitrile Gasket with Screws  
**Series Number :** 121012  
**Status :** Active  
**Product Category :** Circular Industrial Connectors  
**Engineering Number :** B152000N2




## Documents & Resources

**Drawings**  
[1210120009\\_sd.pdf](#)

**Specifications**  
[PK-121012-B15-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements  
- Eu RoHS  
- REACH SVHC  
- Low-Halogen

Multiple Part Industry Compliance Documents  
- IPC 1752A Class C  
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Circular Industrial Connectors
Series	121012
Description	mPm DIN Base, Form B-11mm, B15 Base, 2 Pole Plus Ground Terminal, 250V AC/300V DC, Black, Nitrile Gasket with Screws
IP Rating	IP65, IP67
Product Name	mPm
Type	Field Attachable Connector
UPC	883906322144

#### Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	250V AC / 300V DC

#### Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Form	B - 11mm
Gender	N/A
Keyway	None
Material - Connector Body	Polypropylene
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	3.175/g

Orientation	Straight
Pitch - Mating Interface	11.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size (AWG)	N/A

---

This document was generated on Apr 22, 2025