
214A021-25/86-0 Product Details



Active

Molded Parts

214A021-25/86-0

214A021-25/86-0

TE Internal Number: 128498-000

Product Highlights View All

- DEF Std 59-97 Issue 3 Type DE, MIS-34867, VG95343 Parts 6, 7, 8, & 9
- Molded Part Type = D Subminiature Boot
- Operating Temperature = -55 - 120 °C
- Adhesive Options = /86 Precoat
- 180°

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Documents | Features | Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Molded Part Type	D Subminiature Boot
Angle	180°
Adhesive Description	High Performance Pre-Coat Adhesive
Size	21
Family Name	214A0

Mechanical Attachment

Adhesive Pre-Coating	With

Dimensions

Cable Diameter Range (mm [in])	5.30 – 10.20 [0.209 – 0.402]
Connector Length (mm [in])	28.00 – 28.20 [1.102 – 1.110]
Connector Width (mm [in])	10.70 [0.421]

Body Features

Material	Fluid Resistant Modified Elastomer

Configuration Features

Material Code	25

Industry Standards

Government/Industry Qualification	No
Approved Standards	DEF Std 59-97 Issue 3 Type DE, MIS-34867, VG95343 Parts 6, 7, 8, & 9
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Environmental

Operating Temperature (°C)	-55 – +120

Operation/Application

Application	General Purpose, Military

Purchasing Information

Downloaded from Arrow.com.

Housing Features

Material Systems Code	25

Adhesive Code	86

Other

Adhesive Options	/86 Precoat
Brand	Raychem

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling



© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved

[+] Provide Website Feedback

Downloaded from Arrow.com.