

[Product mass](#)
[Precautions for use](#)
[General notes](#)

F-4000-B

made in JAPAN


Screw Cap

2015-01-05

[Notice of partial product changes.](#) PDF

[See other change notifications](#)


E101405



Order model number

Order model number F-4000-B

Order example F-4000-B

[Basic information](#)
[Dimension](#)
[Soldering heat resistance conditions](#)
[Conformity product / Mate product](#)
[Download](#)

Mating fuse size

6.4mm×30mm

[Add to My List](#) >

[Sample request \(Only available in Japan\)](#) >

Basic information

Rating	250V-10A
Insulation resistance	DC500V, 100MΩ Min
Withstand voltage	AC2000V (1minute)
Certificates & Approvals	UL・CSA(C-UL)
Main insulator	Phenolic (UL94V-0)
Cap insulator	PBT (UL94V-0)
Terminal type	Soldering
Body color	B (Black)
Panel thickness	4.5mm Max
Nut torque	1.2N・m Max
Old model number	F-7105
Caution	1.Due to bottom terminal designed movable, it must away from any other article such as wire or components.

List of partial product change notifications

2015-01-05

[Notice of partial product changes.](#) PDF

2009-12-15

[Notice of partial product changes.](#) PDF

Related products

F-120-B


[F-120-B](#)
[Add to My List](#)
[Home](#)
[Product search](#)
[Product Category](#)
[About SATO PARTS](#)
[News classification](#)
[Contact us](#)
[Video channel](#)
[Download brochure](#)
[Environmental initiatives](#)
[Privacy policy](#)
[Cookie policy](#)
[Download terms](#)
[Terms of Use](#)