

Representative Image

Catalog No. TC5142

Description: SADDLE SPRT BASE NAT NYL SCREW MNT

UPC No 5414363058830

Home > Wire & Cable Management > Ty-Rap > Cable tie mounts

Saddle Support Mounting Base, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length of 23.42mm (0.922 Inches), Width of 14.29mm (0.563 Inches), Height of 10.72mm (0.422 Inches), Mount with #10 Screw, 100 Pack

Descriptors

Category	Cable tie mounts
Special Features	This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

Classifications

Brand Name	Ty-Rap

Dimensions

Mount Size	#10

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Length	23.42 mm
Length	0.92 inch
Width	14.29 mm
Width	0.563 inch
Height	10.72 mm
Height	0.42 inch

Downloaded from Arrow.com.

ETIM	EC000449 Mounting base and -element for cable ties
Type of fastening	Other
Material	Plastic
Material quality	Polyamide (PA)
Colour	Natural colour

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	ZODZ	N/A	N/A

Downloaded from Arrow.com.