



Pushing Performance  
Since 1945

# Crimp die 10mm<sup>2</sup> for 120 kN tool



Image is for illustration purposes only. Please refer to product description.

Part number	09 99 000 0862
Specification	Crimp die 10mm <sup>2</sup> for 120 kN tool
HARTING eCatalogue	<a href="https://harting.com/09990000862">https://harting.com/09990000862</a>

## Identification

Category	Tools
Type of tool	Crimp die
Description of the tool	for 120 kN tool

## Version

Details	Identification 6
	TC 70, TC 100
	Pressing width 10 mm
Pack contents	Supplied as a pair

## Technical characteristics

Conductor cross-section	10 mm <sup>2</sup>
Cycles cleaning / inspection	100
Cycles crimp check	1,000
Cycles service / maintenance	35.000

## Specifications and approvals

Specifications	DIN 46235
----------------	-----------

## Commercial data

Packaging size	1
Net weight	222 g
Country of origin	Germany
European customs tariff number	82073090



Pushing Performance  
Since 1945

Commercial data

GTIN	5713140108059
ETIM	EC001282
eCl@ss	21043852 Insert for crimp tool