

# YSV18BOX, Uninsulated Splice For 22 - 18 AWG

By Burndy  
Catalog # [YSV18BOX](#)

Uninsulated Splice For 22 - 18 AWG



## Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating provides durable long lasting resistance to corrosion
- Positive center wire stops for proper dept of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion

## Application

For All Heavy Duty Industrial And General Purpose Applications

## Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

## Conductor

Conductor - Copper Str Size	<ul style="list-style-type: none"> <li>• 22</li> <li>• 20</li> <li>• 18</li> </ul>
Conductor - Copper Solid Size	<ul style="list-style-type: none"> <li>• 20</li> <li>• 18</li> </ul>
Conductor - Copper Str Aircraft Size	<ul style="list-style-type: none"> <li>• AN 22</li> <li>• AN 20</li> <li>• AN 18</li> </ul>
Conductor Size	22 - 18 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> </ul>

- CU C Solid-Size
- CU C Str Aircraft-Size

## Configuration

Connector Type Seamless Butt Splice

## Current

Voltage - Maximum 35000 V

## Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.12 in
Dimension - L Length Overall mm	16 mm
Package Height	0.000 in
Dimension - Strip Length inch	1/4 in
Dimension - Length Overall inch	0.62 in

## General

Trade Name	HYLINK™
Sub Brand	HYLINK
Plated	Y
Feature - Barrel Style	Chamfered
Type	Splice
UPC 14 Digit GTIN	00781810543801
Material	Copper
Plating Type	Tin
UPC	781810543801

## Logistics

Minimum Pack Quantity	100
Carton Quantity	1200
Pallet Quantity	99999

## Product Assets

[Catalog \[English\]](#)