



Part Number : [1200688219](#)
Product Description : Brad Safety Micro-Change (M12) Drop Wye, 4 Poles, A-Coded, Female/Female with Male Drop
Series Number : 120068
Status : Active
Product Category : Industrial Tees and Splitters
Engineering Number : SAFESPLIT000



Documents & Resources

Drawings

[1200688219 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	120068
Description	Brad Safety Micro-Change (M12) Drop Wye, 4 Poles, A-Coded, Female/Female with Male Drop
IP Rating	IP67
Product Name	Brad Safety, Micro-Change (M12)
Type	Drop Wye
UPC	889056564021

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Drop Connector	Micro-Change (M12)
Drop Gender	Male
Keyway	A-Coded
LED Indicator	None
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Net Weight	33.664/g
Poles	4

Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Female
Temperature Range - Operating	-25°C to +90°C

This document was generated on Sep 22, 2025