

No Image

VG-4501CA.
VCXO/VCSO

Product No. / Ordering code :X1G0037710002

Brief sheet			Data sheet	ROHS	REACH
—	—	—	—	—	—
English	Japanese	Chinese	English	English	English

Specification

Frequency	122.880000 MHz	Operating temperature	-40 to +85 °C
Output Wave	CMOS	Osc Type	VCXO/VCSO
Supply voltage	3.13 to 3.46 V	Model name item name use	VG-4501CA.
Supply voltage (typ)	3.3 V	Frequency control range	N/A ppm
Size (LxWxH):	7.00 x 5.00 x 1.60 mm	Frequency aging	Included absolute pull range
Absolute Pull Range	+/-50ppm (min)	Current consumption	25 mA Max
Control voltage	1.65+/-1.65V	Frequency stability	GGCT
Fo/temp.characteristics tolerance	+/-50 ppm		

[Back](#)

PRODUCTS

- ▶ TCXO
- ▶ VCXO
- ▶ OCXO
- ▶ Crystal Oscillator
- ▶ Real Time Clock
- ▶ Crystal Unit
- ▶ Sensor
- ▶ Timing Module
- ▶ Epson Products for Car Electronics

APPLICATIONS

- ▶ Wired network
- ▶ Measurement instrument
- ▶ Factory automation
- ▶ Security
- ▶ Broadcasting & Audio
- ▶ Automotive

IC Partners

- ▶ Circuit design information
- ▶ IC Partners information

INFORMATION

- ▶ Support
- ▶ Technical Information
- ▶ Precaution
- ▶ Discontinue products
- ▶ Product Change Notification / Engineering Change Notification Announcement
- ▶ Higher Quality / Green Purchasing / Business continuity management
- ▶ Sales Office and Plants
- ▶ Articles

NEWS

- ▶ News Release
- ▶ What's new
- ▶ New products

CONTACT

- ▶ Contact
- ▶ Online distributor

