Product Line

Single Pair Ethernet
ZConnect
Ceres
X-Lok
M Series
Accessory
M5
Guided M8
M8
M10.5
M12 (A)
M12 (B)
M12 (D)
M12 (I)
M12 (K)
M12 (L)
M12 (S)
M12 (T)
M23
FLOS & FLOS+
Power
RBL
HS-Lok
NMEA 2000
Heavy Duty Shielded
RJ
USB
SSL
HDMI
DVI
Fiber Optic
RF
Cable Joiner
Cable Gland
Pressure Relief Vent
LED Light Guide
D-Sub





MSAS-08PMMT-EE0001

- Operating Temperature: -55°C ~ +125°C
- Transmission Speed: N/A
- Shielded: Plastic, Shielded
- Jacket Material: N/A
- Certificate: UL2238

You must login first for view the price

Quantity − 1 + Check Stock

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type | Search



M Series, Accessory
APPM-AAAMA012-001
N/A



M Series, Accessory
APPM-AAAMA012-002
N/A



M Series, Accessory, Nut
APTM-BMZMA012-001
N/A



M Series, Accessory, Nut
APTM-BMZMA012-002
N/A

Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current: **2A**	Connector Type: **SMT**
Shielded: **Plastic, Shielded**	No. of Contacts: **08**
Connector Gender: **Male**	Backshell: **N/A**
Mating Style: **N/A**	IP Rating: **Non-waterproof**
Assembly Style: **SMT 180°**	

More Options

People Also Bought

Downloaded from Arrow.com.